

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319797

Luminaire Tested: LDSQA3D05R259840DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R259840DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 512.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319797
CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1319797

CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	94	92	90	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	92	90	88	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	90	87	85	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	88	85	83	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	86	83	81	80
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	84	81	79	78
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	82	79	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	423616	423616	423616
5°	390606	391488	392300
10°	303276	304378	306022
15°	149877	156189	156243
20°	50474	53846	51482
25°	20903	23221	21492
30°	8193	10301	8273
35°	2144	4205	2229
40°	787	1686	787
45°	97	487	97
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 487 cd/sqm



TEST NUMBER: P1319797

CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.3	38.9
10°-20°	241.1	47.1
20°-30°	58.9	11.5
30°-40°	11.4	2.2
40°-50°	1.3	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	499.3	97.5
0°-40°	510.7	99.7
0°-60°	512.0	100.0
0°-90°	512.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2460	2460	2460	2460	2460	
5°	2259	2262	2264	2274	2269	199
15°	841	861	876	885	876	237
25°	110	116	122	117	113	56
35°	10	14	20	14	11	9
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319797

CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2459.7	2459.7	2459.7	2459.7	2459.7
1°	2450.3	2451.9	2452.3	2454.6	2449.9
2°	2427.9	2428.3	2429.5	2434.2	2429.9
3°	2386.7	2389.4	2389.8	2396.1	2397.3
4°	2330.5	2332.1	2335.2	2345.8	2336.4
5°	2259.4	2262.5	2264.5	2274.3	2269.2
6°	2171.4	2172.2	2176.5	2187.9	2180.8
7°	2081.9	2081.5	2081.9	2090.9	2088.9
8°	1973.8	1971.9	1978.2	1989.2	1996.6
9°	1861.1	1863.8	1867.8	1878.4	1869.7
10°	1734.2	1741.7	1740.5	1741.3	1749.9
11°	1588.1	1590.5	1590.9	1599.1	1597.9
12°	1416.4	1416.4	1429.4	1442.8	1438.4
13°	1243.2	1255.4	1246.8	1249.5	1266.8
14°	1041.3	1050.7	1062.5	1073.5	1064.9
15°	840.6	860.6	876.0	884.6	876.3
17.5°	481.6	488.3	501.2	502.8	497.7
20°	275.4	283.6	293.8	290.7	280.9
22.5°	173.2	175.6	185.8	180.7	178.3
25°	110.0	115.9	122.2	117.1	113.1
27.5°	68.3	72.3	79.0	73.5	69.1
30°	41.2	44.8	51.8	44.4	41.6
32.5°	21.6	26.7	32.6	27.1	21.6
35°	10.2	14.5	20.0	14.5	10.6
37.5°	6.3	7.9	12.2	7.9	6.3
40°	3.5	5.1	7.5	5.1	3.5
42.5°	1.6	2.7	3.5	2.7	2.0
45°	0.4	1.2	2.0	1.2	0.4
47.5°	0.0	0.0	1.2	0.4	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319797
CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)