

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319800

Luminaire Tested: LDSQA3D05R259840DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R259840DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 98CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 440.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319800
CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQPHR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1319800
 CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	410596	410596	410596
5°	372091	375479	377312
10°	279720	281713	283007
15°	138502	134383	143334
20°	39111	39771	40192
25°	6784	12827	8057
30°	2645	2724	2804
35°	820	904	904
40°	270	360	270
45°	195	97	195
50°	107	0	107
55°	120	0	120
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 195 cd/sqm



TEST NUMBER: P1319800
 CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	43.0
10°-20°	213.6	48.5
20°-30°	33.1	7.5
30°-40°	3.3	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	436.1	99.1
0°-40°	439.5	99.9
0°-60°	440.0	100.0
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2384	2384	2384	2384	2384	
5°	2152	2156	2172	2180	2182	188
15°	777	771	754	787	804	213
25°	36	53	68	51	42	30
35°	4	4	4	5	4	3
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319800
 CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2384.1	2384.1	2384.1	2384.1	2384.1
1°	2374.3	2377.5	2373.9	2377.9	2377.5
2°	2349.6	2352.8	2348.4	2350.8	2350.8
3°	2299.0	2305.7	2309.6	2312.4	2314.7
4°	2232.3	2239.8	2245.7	2252.7	2252.7
5°	2152.3	2156.2	2171.9	2180.5	2182.5
6°	2057.0	2072.6	2084.4	2101.7	2091.1
7°	1961.6	1974.6	1991.0	1993.8	2001.2
8°	1853.3	1867.1	1882.4	1879.6	1873.3
9°	1721.5	1741.5	1759.6	1753.7	1761.5
10°	1599.5	1611.7	1610.9	1605.0	1618.3
11°	1457.9	1460.6	1445.3	1469.3	1454.7
12°	1290.0	1292.3	1272.7	1296.2	1311.1
13°	1129.1	1123.6	1096.5	1127.5	1146.4
14°	943.9	945.9	911.4	971.4	966.7
15°	776.8	771.3	753.7	787.4	803.9
17.5°	413.9	417.4	413.1	430.0	440.6
20°	213.4	219.3	217.0	224.0	219.3
22.5°	110.6	118.9	121.2	115.7	100.8
25°	35.7	53.0	67.5	51.4	42.4
27.5°	21.6	21.2	33.0	22.8	23.1
30°	13.3	12.9	13.7	13.7	14.1
32.5°	7.5	7.8	7.5	8.2	7.8
35°	3.9	4.3	4.3	4.7	4.3
37.5°	2.4	2.7	2.7	2.7	2.4
40°	1.2	1.6	1.6	1.2	1.2
42.5°	0.8	0.8	0.8	0.8	0.8
45°	0.8	0.4	0.4	0.4	0.8
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.4	0.0	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.4	0.0	0.0	0.0	0.4
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319800
CATALOG NUMBER: LDSQA3D05R259840DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)