

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320682

Luminaire Tested: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 80CRI , 3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 266.0 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320682  
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

### Luminous Intensity Polar Plot



0% Up  
100% Dn

— 0°-180°    - - 45°-225°    - · - · 90°-270°



TEST NUMBER: P1320682

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	94	92	90	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	92	90	88	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	90	87	85	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	88	85	83	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	86	83	81	80
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	84	81	79	78
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	82	79	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	220083	220083	220083
5°	202927	203394	203809
10°	157566	158126	158983
15°	77863	81143	81179
20°	26227	27968	26740
25°	10851	12067	11174
30°	4256	5349	4295
35°	1114	2187	1156
40°	405	877	405
45°	49	244	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 244 cd/sqm



TEST NUMBER: P1320682

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.5	38.9
10°-20°	125.2	47.1
20°-30°	30.6	11.5
30°-40°	5.9	2.2
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	259.4	97.5
0°-40°	265.3	99.7
0°-60°	266.0	100.0
0°-90°	266.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	266.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1278	1278	1278	1278	1278	
5°	1174	1176	1176	1182	1179	103
15°	437	447	455	460	455	123
25°	57	60	64	61	59	29
35°	5	8	10	8	6	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320682

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1277.9	1277.9	1277.9	1277.9	1277.9
1°	1273.0	1273.8	1274.0	1275.3	1272.8
2°	1261.4	1261.6	1262.2	1264.6	1262.4
3°	1239.9	1241.4	1241.6	1244.8	1245.5
4°	1210.8	1211.6	1213.2	1218.7	1213.8
5°	1173.8	1175.5	1176.5	1181.6	1178.9
6°	1128.1	1128.5	1130.8	1136.7	1133.0
7°	1081.6	1081.4	1081.6	1086.3	1085.3
8°	1025.5	1024.4	1027.7	1033.4	1037.3
9°	966.9	968.3	970.4	975.9	971.4
10°	901.0	904.9	904.2	904.7	909.1
11°	825.1	826.3	826.5	830.8	830.2
12°	735.9	735.9	742.6	749.6	747.3
13°	645.9	652.2	647.7	649.2	658.1
14°	541.0	545.9	552.0	557.7	553.2
15°	436.7	447.1	455.1	459.6	455.3
17.5°	250.2	253.7	260.4	261.2	258.6
20°	143.1	147.3	152.6	151.0	145.9
22.5°	90.0	91.2	96.5	93.9	92.6
25°	57.1	60.2	63.5	60.8	58.8
27.5°	35.5	37.5	41.0	38.2	35.9
30°	21.4	23.3	26.9	23.1	21.6
32.5°	11.2	13.9	16.9	14.1	11.2
35°	5.3	7.6	10.4	7.6	5.5
37.5°	3.3	4.1	6.3	4.1	3.3
40°	1.8	2.7	3.9	2.7	1.8
42.5°	0.8	1.4	1.8	1.4	1.0
45°	0.2	0.6	1.0	0.6	0.2
47.5°	0.0	0.0	0.6	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320682  
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)