

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320839

Luminaire Tested: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-77)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 80CRI , 3LSQCA45R 1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 4.01 / 0.66 / 1.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320839
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° ···· 90°-270°



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	50
5	75	62	52	46	73	61	52	45	58	51	45	56	50	44	55	49	44	42
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35
7	62	48	38	32	60	47	38	32	45	37	32	44	37	31	42	36	31	29
8	57	42	33	27	55	41	33	27	40	32	27	39	32	26	38	31	26	24
9	52	38	29	23	50	37	29	23	36	28	23	35	28	22	34	27	22	20
10	48	34	25	19	46	33	25	19	32	25	19	31	24	19	30	24	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	1894	1894	1894	1894	1894
5°	2057	2023	1867	1677	1642
10°	2151	1976	1661	1434	1434
15°	3085	1926	1355	1230	1266
20°	7734	2071	1063	1063	1191
25°	35934	2641	817	988	1102
30°	109257	3580	636	895	1114
35°	184658	4142	547	862	1093
40°	216457	4092	427	877	1169
45°	227947	2898	365	950	1267
50°	216970	1742	348	991	1393
55°	181808	721	390	1111	1621
60°	101784	138	448	1274	1791
65°	17564	82	448	1426	2038
70°	302	101	554	1511	2266
75°	266	133	732	1730	2595
80°	198	198	893	1884	2975
85°	0	395	1778	2174	3359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 46°
 Luminance: 229578 cd/sqm



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.0	0.4
10°-20°	2.8	1.2
20°-30°	14.7	6.1
30°-40°	63.6	26.5
40°-50°	90.7	37.8
50°-60°	56.2	23.4
60°-70°	8.5	3.6
70°-80°	1.6	0.7
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	18.5	7.7
0°-40°	82.1	34.2
0°-60°	229.0	95.4
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	11	11	11	11	11	
5°	12	12	11	10	10	1
15°	17	11	8	7	7	6
25°	189	14	4	5	6	113
35°	878	20	3	4	5	527
45°	936	12	2	4	5	707
55°	606	2	1	4	5	516
65°	43	0	1	4	5	88
75°	0	0	1	3	4	0
85°	0	0	1	1	2	0
90°	0	0	0	0	0	



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0	11.0
2.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.0	10.8
5°	11.9	11.9	11.7	11.7	11.7	11.7	11.7	11.7	11.3	10.8	10.2
7.5°	12.1	12.1	11.9	11.9	11.9	11.9	11.7	11.5	11.0	10.2	9.5
10°	12.3	12.3	12.3	12.3	12.1	11.9	11.7	11.3	10.6	9.5	8.9
12.5°	13.9	13.9	13.6	13.2	12.8	12.3	11.9	11.0	9.7	8.7	8.0
15°	17.3	17.1	16.7	16.0	15.2	14.1	13.2	10.8	8.9	7.6	7.1
17.5°	24.3	23.8	23.2	21.0	19.1	17.1	15.4	10.8	8.0	6.7	6.3
20°	42.2	42.5	37.9	32.7	28.4	23.6	19.3	11.3	7.1	5.8	5.6
22.5°	88.2	84.7	73.9	61.3	46.8	36.2	27.3	12.3	6.3	5.0	5.0
25°	189.1	175.9	149.7	113.1	79.7	56.5	39.6	13.9	5.6	4.3	4.5
27.5°	345.3	333.4	280.8	211.5	140.4	85.4	53.7	15.8	5.0	3.7	4.1
30°	549.4	516.5	447.8	346.6	234.6	130.6	72.1	18.0	4.1	3.2	3.9
31°	613.1	598.0	514.3	401.0	274.9	155.1	79.9	18.6	3.9	3.2	3.7
32°	688.7	661.9	586.9	460.6	315.9	177.0	89.3	19.3	3.7	2.8	3.7
33°	756.3	730.3	639.1	513.0	357.3	201.9	99.2	19.5	3.2	2.8	3.5
34°	827.4	791.9	701.5	567.8	399.7	228.8	108.3	19.7	3.0	2.6	3.5
35°	878.3	842.8	755.2	611.2	436.3	252.6	118.7	19.7	2.8	2.6	3.2
36°	917.7	886.5	801.6	655.8	472.7	274.1	127.0	19.7	2.4	2.4	3.2
37°	944.8	915.1	832.8	694.2	500.5	293.1	134.3	19.7	2.2	2.4	3.2
38°	958.0	933.3	862.9	722.1	527.3	308.1	140.2	19.3	1.9	2.2	3.0
39°	963.7	943.5	881.3	745.7	547.5	321.1	144.5	18.8	1.7	2.2	3.0
40°	962.8	945.2	891.7	762.0	563.7	330.0	146.9	18.2	1.5	1.9	3.0
41°	957.8	942.7	897.2	775.8	573.5	336.0	147.5	17.5	1.3	1.9	2.8
42°	952.2	938.3	898.9	783.2	579.8	338.0	145.8	16.7	1.3	1.7	2.8
43°	946.3	933.6	898.9	785.6	581.3	336.7	143.0	15.2	1.1	1.7	2.8
44°	941.6	929.4	896.1	784.9	578.0	331.7	137.8	13.4	0.9	1.7	2.8
45°	935.9	924.0	892.4	780.8	571.7	323.2	131.3	11.9	0.6	1.5	2.8
46°	926.0	916.7	885.9	772.4	561.8	311.5	123.1	10.8	0.4	1.5	2.6
47°	906.7	898.7	873.3	759.8	548.6	297.7	114.6	9.7	0.4	1.5	2.6
48°	867.9	867.7	848.2	736.4	527.5	280.3	105.7	8.7	0.4	1.5	2.6
49°	830.4	826.5	802.3	695.2	497.4	259.5	96.4	7.8	0.2	1.5	2.6
50°	809.8	801.4	761.5	646.7	458.9	230.7	86.4	6.5	0.2	1.3	2.6
51°	788.4	776.3	729.2	602.9	412.9	203.0	75.6	5.2	0.2	1.3	2.4
52°	749.6	738.1	685.5	561.1	368.3	174.6	65.2	4.3	0.2	1.3	2.6
53°	707.8	691.3	634.1	515.2	329.1	149.5	54.6	3.7	0.2	1.3	2.4
54°	655.2	647.8	582.1	458.9	283.2	125.2	44.8	3.0	0.2	1.3	2.4
55°	605.5	594.7	526.5	401.2	241.6	102.7	37.5	2.4	0.2	1.3	2.4
56°	542.3	526.0	462.1	348.4	199.3	82.8	31.6	1.9	0.2	1.3	2.4
57°	466.9	449.6	399.1	289.7	156.4	63.0	26.4	1.5	0.2	1.3	2.4
58°	395.0	380.0	325.8	223.6	117.9	43.8	21.9	1.1	0.2	1.1	2.4
59°	341.2	324.8	271.0	172.0	81.9	32.3	16.5	0.9	0.2	1.3	2.4
60°	295.5	274.3	218.2	133.2	58.5	23.2	12.1	0.4	0.4	1.3	2.4
62.5°	170.3	150.4	104.2	54.2	24.0	11.9	5.8	0.2	0.4	1.3	2.4
65°	43.1	38.3	24.9	11.7	6.7	4.1	2.2	0.2	0.4	1.1	2.2



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
67.5°	1.5	1.5	1.5	1.3	1.1	0.9	0.4	0.2	0.4	1.1	2.2
70°	0.6	0.6	0.6	0.4	0.4	0.2	0.2	0.2	0.4	1.1	1.9
72.5°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.6	1.1	1.7
75°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.6	1.1	1.7
77.5°	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.9	1.5
80°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.9	1.3
82.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.9	1.1
85°	0.0	0.0	0.0	0.0	0.0	0.2	0.0	0.2	0.6	0.9	0.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.6	0.9	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	11.0	11.0	11.0
2.5°	10.4	10.4	10.4
5°	9.7	9.7	9.5
7.5°	9.1	8.9	8.9
10°	8.2	8.2	8.2
12.5°	7.6	7.6	7.6
15°	6.9	7.1	7.1
17.5°	6.3	6.7	6.7
20°	5.8	6.3	6.5
22.5°	5.4	5.8	6.1
25°	5.2	5.6	5.8
27.5°	4.8	5.4	5.8
30°	4.5	5.2	5.6
31°	4.5	5.2	5.4
32°	4.3	5.2	5.4
33°	4.3	5.2	5.4
34°	4.3	5.0	5.4
35°	4.1	5.0	5.2
36°	4.1	5.0	5.2
37°	4.1	5.0	5.4
38°	4.1	5.0	5.2
39°	3.9	5.0	5.2
40°	3.9	5.0	5.2
41°	3.9	5.0	5.2
42°	3.9	5.0	5.2
43°	3.9	5.0	5.2
44°	3.9	4.8	5.2
45°	3.9	4.8	5.2
46°	3.9	5.0	5.2
47°	3.9	5.0	5.4
48°	3.9	4.8	5.2
49°	3.7	4.8	5.2
50°	3.7	4.8	5.2
51°	3.7	5.0	5.4
52°	3.7	5.0	5.4
53°	3.7	5.0	5.4
54°	3.7	5.0	5.2
55°	3.7	5.0	5.4
56°	3.7	5.0	5.2
57°	3.7	5.0	5.2
58°	3.7	4.8	5.2
59°	3.7	4.8	5.2
60°	3.7	4.8	5.2
62.5°	3.5	4.8	5.2
65°	3.5	4.5	5.0



TEST NUMBER: P1320839

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQCA45R 1MMS_5000K

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
67.5°	3.2	4.5	4.8
70°	3.0	4.3	4.5
72.5°	2.8	4.1	4.3
75°	2.6	3.7	3.9
77.5°	2.2	3.2	3.7
80°	1.9	2.8	3.0
82.5°	1.5	2.4	2.6
85°	1.1	1.7	1.7
87.5°	0.4	0.9	0.9
90°	0.0	0.0	0.0

(END OF REPORT)