

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320871

Luminaire Tested: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , 3LSQPHR1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 231.0 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320871  
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1320871

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	93	93	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90	90	90	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87	87	87	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	85	85	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	82	82	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	80	80	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	77	77	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	75	75	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	131079	131079	131079
5°	128813	128554	128277
10°	118061	114511	111730
15°	84531	81839	80858
20°	39203	40559	41970
25°	9292	13226	13796
30°	2724	3122	3520
35°	631	1009	925
40°	135	270	180
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 57 cd/sqm



TEST NUMBER: P1320871

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.3	29.6
10°-20°	122.2	52.9
20°-30°	36.7	15.9
30°-40°	3.5	1.5
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.2	98.4
0°-40°	230.8	99.9
0°-60°	231.0	100.0
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	761	761	761	761	761	
5°	745	745	744	743	742	69
15°	474	471	459	457	454	125
25°	49	54	70	73	73	31
35°	3	4	5	5	4	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320871

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	761.1	761.1	761.1	761.1	761.1
1°	760.7	760.7	760.3	760.3	759.5
2°	758.9	759.1	758.3	758.1	757.5
3°	756.1	755.5	755.5	755.1	754.7
4°	751.7	750.5	750.1	750.3	749.5
5°	745.1	744.9	743.6	742.6	742.0
6°	738.0	736.6	733.6	731.0	730.4
7°	727.2	724.3	721.7	716.3	715.5
8°	714.1	709.3	703.8	696.2	695.8
9°	698.0	690.2	682.5	672.3	668.7
10°	675.1	667.9	654.8	645.9	638.9
11°	646.7	637.7	622.4	611.6	605.9
12°	614.4	606.1	588.2	578.4	570.3
13°	573.0	566.1	549.4	538.6	532.2
14°	525.1	519.9	504.0	499.2	497.0
15°	474.1	470.6	459.0	457.0	453.5
17.5°	349.0	343.0	336.5	337.7	338.8
20°	213.9	222.3	221.3	225.6	229.0
22.5°	106.6	117.4	129.9	137.5	141.3
25°	48.9	53.9	69.6	72.6	72.6
27.5°	24.7	25.9	32.8	33.4	35.0
30°	13.7	14.7	15.7	17.5	17.7
32.5°	7.0	8.2	8.6	9.6	9.2
35°	3.0	4.0	4.8	5.2	4.4
37.5°	1.4	1.8	2.6	2.4	1.8
40°	0.6	0.8	1.2	1.0	0.8
42.5°	0.4	0.4	0.6	0.4	0.4
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320871  
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)