

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320523

Luminaire Tested: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320523

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1320523

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	91	91	90
6	103	97	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	90	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	88	92	90	88	88	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	90	88	87	87	87	86
9	97	92	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	85	85	84
10	95	90	87	84	95	90	86	84	89	86	84	88	86	84	88	86	84	84	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	395044	395044	395044
5°	321627	322681	322059
10°	150029	151376	149469
15°	47106	47516	47231
20°	18657	19409	18071
25°	7544	9121	7278
30°	3023	4156	2864
35°	904	1829	841
40°	270	674	225
45°	49	146	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 146 cd/sqm

TEST NUMBER: P1320523

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.6	56.1
10°-20°	85.9	33.6
20°-30°	21.7	8.5
30°-40°	4.4	1.7
40°-50°	0.4	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.2	98.1
0°-40°	255.6	99.8
0°-60°	256.0	100.0
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2294	2294	2294	2294	2294	
5°	1860	1857	1866	1862	1863	143
15°	264	266	266	263	265	86
25°	40	43	48	42	38	20
35°	4	6	9	6	4	4
45°	0	0	1	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1320523

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2293.8	2293.8	2293.8	2293.8	2293.8
1°	2273.1	2280.8	2276.7	2280.0	2276.3
2°	2223.9	2234.2	2231.0	2230.0	2232.8
3°	2137.2	2149.2	2148.8	2145.7	2140.9
4°	2019.0	2014.1	2021.6	2020.8	2012.5
5°	1860.4	1857.0	1866.5	1861.9	1862.9
6°	1666.5	1681.4	1678.2	1678.6	1682.4
7°	1458.1	1466.2	1473.1	1478.7	1470.9
8°	1266.7	1264.7	1265.3	1271.8	1249.9
9°	1052.5	1065.1	1057.0	1044.0	1052.3
10°	857.9	865.6	865.6	854.3	854.7
11°	684.0	690.3	685.8	688.7	670.8
12°	551.4	535.8	532.1	535.0	534.8
13°	421.0	422.0	421.0	420.8	418.7
14°	330.1	335.3	333.1	327.6	325.2
15°	264.2	266.5	266.5	262.6	264.9
17.5°	158.7	161.4	162.0	159.4	159.4
20°	101.8	103.1	105.9	102.1	98.6
22.5°	62.8	65.4	70.3	64.6	61.8
25°	39.7	43.3	48.0	42.5	38.3
27.5°	24.9	27.9	32.0	26.7	24.1
30°	15.2	17.2	20.9	16.8	14.4
32.5°	8.5	10.1	13.2	9.7	8.1
35°	4.3	5.7	8.7	5.5	4.0
37.5°	2.4	3.0	5.5	2.6	2.2
40°	1.2	1.6	3.0	1.6	1.0
42.5°	0.4	0.8	1.2	0.8	0.4
45°	0.2	0.4	0.6	0.4	0.2
47.5°	0.0	0.0	0.2	0.0	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320523

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQCDR1MB_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)