

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320558

Luminaire Tested: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320558  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , 3LSQPHRL1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 158.0 lumens  
Efficiency: N/A  
Efficacy: 54.5 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.46 / 0.48  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320558  
CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°



TEST NUMBER: P1320558  
 CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	94
2	109	104	101	97	107	103	99	96	99	97	94	97	94	92	94	92	90	90	90	90	89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	85	85	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	72	87	80	75	71	79	74	71	77	74	71	76	73	70	70	70	70	69
8	85	77	72	68	84	76	72	68	75	71	68	74	71	68	74	70	67	67	67	67	66
9	82	74	69	65	81	73	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	82288	82288	82288
5°	74529	74667	74771
10°	56276	56416	56696
15°	36498	36890	37621
20°	21975	22231	22525
25°	12846	13112	13302
30°	7537	7796	7915
35°	4646	4815	4899
40°	3058	3147	3192
45°	2119	2168	2216
50°	1581	1634	1688
55°	1291	1351	1351
60°	1102	1102	1102
65°	978	978	978
70°	806	906	906
75°	799	799	799
80°	595	793	793
85°	395	395	395

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 67.5°  
 Vertical Angle: 45°  
 Luminance: 2216 cd/sqm



TEST NUMBER: P1320558

CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.6	23.8
10°-20°	57.5	36.4
20°-30°	32.7	20.7
30°-40°	14.9	9.4
40°-50°	7.2	4.5
50°-60°	4.0	2.5
60°-70°	2.4	1.5
70°-80°	1.3	0.8
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.9	81.0
0°-40°	142.8	90.4
0°-60°	154.0	97.5
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	478	478	478	478	478	
5°	431	431	432	432	432	38
15°	205	206	207	210	211	57
25°	68	68	69	70	70	32
35°	22	22	23	23	23	15
45°	9	9	9	9	9	7
55°	4	4	4	4	4	4
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1320558  
 CATALOG NUMBER: LDSQA3D02R15B2750DE010 3LSQPHRL1MMS\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	477.8	477.8	477.8	477.8	477.8
1°	477.4	476.2	475.8	475.5	475.1
2°	471.3	470.3	470.1	470.1	469.9
3°	462.8	460.9	461.1	460.5	459.9
4°	448.4	447.6	448.0	448.4	447.6
5°	431.1	430.9	431.9	431.9	432.5
6°	413.3	413.1	412.5	414.1	414.9
7°	390.5	391.8	393.4	392.6	393.2
8°	369.8	368.4	369.0	371.1	371.3
9°	345.5	344.5	347.1	347.9	348.1
10°	321.8	322.8	322.6	325.4	324.2
12.5°	259.9	261.5	263.3	264.6	265.8
15°	204.7	205.7	206.9	209.8	211.0
17.5°	157.4	158.7	159.9	162.3	162.7
20°	119.9	120.5	121.3	123.6	122.9
22.5°	89.7	90.7	91.5	92.5	93.1
25°	67.6	67.6	69.0	69.6	70.0
27.5°	50.3	50.7	51.7	52.5	52.3
30°	37.9	38.5	39.2	39.6	39.8
32.5°	29.2	29.2	29.8	30.4	30.6
35°	22.1	22.5	22.9	23.3	23.3
37.5°	17.2	17.4	17.9	18.1	18.1
40°	13.6	13.6	14.0	14.2	14.2
42.5°	10.8	11.0	11.2	11.4	11.4
45°	8.7	8.7	8.9	9.1	9.1
47.5°	7.1	7.1	7.3	7.5	7.5
50°	5.9	6.1	6.1	6.3	6.3
52.5°	5.1	5.1	5.1	5.3	5.3
55°	4.3	4.3	4.5	4.5	4.5
57.5°	3.7	3.7	3.7	3.9	3.9
60°	3.2	3.2	3.2	3.2	3.2
62.5°	2.8	2.8	2.8	2.8	2.8
65°	2.4	2.4	2.4	2.4	2.4
67.5°	2.0	2.0	2.0	2.2	2.2
70°	1.6	1.8	1.8	1.8	1.8
72.5°	1.4	1.4	1.4	1.4	1.4
75°	1.2	1.2	1.2	1.2	1.2
77.5°	1.0	1.0	1.0	1.0	1.0
80°	0.6	0.8	0.8	0.8	0.8
82.5°	0.4	0.4	0.4	0.4	0.4
85°	0.2	0.2	0.2	0.2	0.2
87.5°	0.0	0.0	0.0	0.0	0.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)