

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320618

Luminaire Tested: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 80CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320618
CATALOG NUMBER: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1320618

CATALOG NUMBER: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	95	93	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	90	93	91	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	88	92	90	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	87	91	88	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	89	87	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	84	88	86	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	291073	291073	291073
5°	251455	253789	254739
10°	151376	152792	160382
15°	52348	51136	55201
20°	13746	12939	12976
25°	3002	3611	4105
30°	1293	1293	1332
35°	715	631	673
40°	315	360	405
45°	97	146	146
50°	54	54	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 146 cd/sqm



TEST NUMBER: P1320618

CATALOG NUMBER: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	53.3
10°-20°	92.0	40.5
20°-30°	11.4	5.0
30°-40°	2.1	0.9
40°-50°	0.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.3	98.8
0°-40°	226.4	99.8
0°-60°	227.0	100.0
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1690	1690	1690	1690	1690	
5°	1454	1454	1468	1467	1474	120
15°	294	283	287	304	310	92
25°	16	18	19	20	22	11
35°	3	3	3	3	3	2
45°	0	1	1	1	1	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320618

CATALOG NUMBER: LDSQA3D02R20B2750DE010 3LSQPHR1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1690.1	1690.1	1690.1	1690.1	1690.1
1°	1682.2	1680.2	1681.8	1678.4	1685.4
2°	1655.3	1653.3	1653.3	1651.3	1652.3
3°	1605.1	1608.4	1606.4	1602.1	1607.6
4°	1536.8	1540.4	1543.7	1543.9	1544.7
5°	1454.5	1453.5	1468.0	1467.0	1473.5
6°	1360.6	1359.4	1365.7	1376.2	1389.2
7°	1257.5	1242.7	1259.5	1280.8	1298.1
8°	1124.0	1127.9	1139.4	1164.5	1178.4
9°	1010.8	988.3	1012.8	1042.7	1057.9
10°	865.6	847.4	873.7	905.2	917.1
12.5°	544.8	529.0	537.5	570.7	576.0
15°	293.6	283.1	286.8	304.0	309.6
17.5°	149.9	140.4	138.3	149.2	150.5
20°	75.0	72.8	70.6	71.6	70.8
22.5°	34.8	37.8	37.4	35.4	37.8
25°	15.8	18.0	19.0	19.8	21.6
27.5°	9.7	9.3	10.7	11.5	11.7
30°	6.5	6.3	6.5	6.7	6.7
32.5°	4.7	4.4	4.2	4.2	4.4
35°	3.4	3.4	3.0	3.2	3.2
37.5°	2.4	2.4	2.2	2.4	2.4
40°	1.4	1.6	1.6	1.6	1.8
42.5°	0.8	1.0	1.0	1.0	1.0
45°	0.4	0.6	0.6	0.6	0.6
47.5°	0.2	0.2	0.2	0.4	0.4
50°	0.2	0.2	0.2	0.2	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)