

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320681

Luminaire Tested: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 260.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320681
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1320681

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100																
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	99	99	99	99	99	99	99	99	99	99	99	99	97																
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	96	96	96	96	96	96	96	96	96	94																
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	93	93	93	93	93	93	93	93	93	93	93	93	92																
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	90	90	90	90	90	90	90	90	90	90	90	90	89																
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	88	88	88	88	88	88	88	88	88	88	88	88	87																
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	85	85	85	85	85	85	85	85	85	85	85	85	84																
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	83	83	83	83	83	83	83	83	83	83	83	83	82																
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	81	81	81	81	81	81	81	81	81	81	81	81	80																
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	79	79	79	79	79	79	79	79	79	79	79	79	78																
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	77	77	77	77	77	77	77	77	77	77	77	77	77																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	215123	215123	215123
5°	198363	198795	199210
10°	154016	154576	155398
15°	76115	79307	79343
20°	25622	27345	26135
25°	10622	11782	10908
30°	4156	5230	4196
35°	1093	2144	1135
40°	405	854	405
45°	49	244	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 244 cd/sqm



TEST NUMBER: P1320681

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.2	38.9
10°-20°	122.4	47.1
20°-30°	29.9	11.5
30°-40°	5.8	2.2
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.5	97.5
0°-40°	259.3	99.7
0°-60°	260.0	100.0
0°-90°	260.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1249	1249	1249	1249	1249	
5°	1147	1149	1150	1155	1152	101
15°	427	437	445	449	445	120
25°	56	59	62	59	57	28
35°	5	7	10	7	5	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320681

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1249.1	1249.1	1249.1	1249.1	1249.1
1°	1244.3	1245.1	1245.3	1246.5	1244.1
2°	1232.9	1233.1	1233.7	1236.1	1233.9
3°	1212.0	1213.4	1213.6	1216.8	1217.4
4°	1183.5	1184.3	1185.9	1191.2	1186.4
5°	1147.4	1148.9	1149.9	1154.9	1152.3
6°	1102.7	1103.1	1105.3	1111.0	1107.5
7°	1057.2	1057.0	1057.2	1061.8	1060.8
8°	1002.3	1001.3	1004.5	1010.1	1013.9
9°	945.1	946.5	948.5	953.9	949.5
10°	880.7	884.5	883.9	884.3	888.6
11°	806.5	807.7	807.9	812.0	811.4
12°	719.3	719.3	725.9	732.7	730.5
13°	631.3	637.5	633.1	634.5	643.3
14°	528.8	533.6	539.6	545.2	540.8
15°	426.9	437.0	444.8	449.2	445.0
17.5°	244.6	247.9	254.5	255.3	252.7
20°	139.8	144.0	149.2	147.6	142.6
22.5°	88.0	89.2	94.3	91.8	90.6
25°	55.9	58.8	62.0	59.4	57.4
27.5°	34.7	36.7	40.1	37.3	35.1
30°	20.9	22.7	26.3	22.5	21.1
32.5°	11.0	13.6	16.6	13.8	11.0
35°	5.2	7.4	10.2	7.4	5.4
37.5°	3.2	4.0	6.2	4.0	3.2
40°	1.8	2.6	3.8	2.6	1.8
42.5°	0.8	1.4	1.8	1.4	1.0
45°	0.2	0.6	1.0	0.6	0.2
47.5°	0.0	0.0	0.6	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320681
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQCDR1MMS_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)