

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320693

Luminaire Tested: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320693
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1320693
 CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	88	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	86	86	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	211834	211834	211834
5°	191967	193713	194663
10°	144311	145342	146007
15°	71462	69322	73940
20°	20179	20509	20728
25°	3496	6613	4162
30°	1372	1412	1452
35°	420	463	463
40°	135	180	135
45°	97	49	97
50°	54	0	54
55°	60	0	60
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 97 cd/sqm



TEST NUMBER: P1320693

CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	43.0
10°-20°	110.2	48.5
20°-30°	17.1	7.5
30°-40°	1.7	0.8
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.0	99.1
0°-40°	226.7	99.9
0°-60°	227.0	100.0
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1110	1112	1120	1125	1126	97
15°	401	398	389	406	415	110
25°	18	27	35	26	22	15
35°	2	2	2	2	2	2
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320693
 CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1230.0	1230.0	1230.0	1230.0	1230.0
1°	1224.9	1226.6	1224.7	1226.8	1226.6
2°	1212.2	1213.8	1211.6	1212.8	1212.8
3°	1186.1	1189.5	1191.5	1193.0	1194.2
4°	1151.7	1155.5	1158.6	1162.2	1162.2
5°	1110.4	1112.4	1120.5	1125.0	1126.0
6°	1061.2	1069.3	1075.4	1084.3	1078.8
7°	1012.0	1018.7	1027.2	1028.6	1032.5
8°	956.2	963.2	971.1	969.7	966.5
9°	888.1	898.5	907.8	904.7	908.8
10°	825.2	831.5	831.1	828.0	834.9
11°	752.1	753.5	745.7	758.0	750.5
12°	665.5	666.7	656.6	668.7	676.4
13°	582.5	579.7	565.7	581.7	591.4
14°	487.0	488.0	470.2	501.2	498.7
15°	400.8	397.9	388.8	406.2	414.7
17.5°	213.5	215.4	213.1	221.8	227.3
20°	110.1	113.1	111.9	115.6	113.1
22.5°	57.1	61.3	62.5	59.7	52.0
25°	18.4	27.3	34.8	26.5	21.9
27.5°	11.1	10.9	17.0	11.7	11.9
30°	6.9	6.7	7.1	7.1	7.3
32.5°	3.8	4.0	3.8	4.3	4.0
35°	2.0	2.2	2.2	2.4	2.2
37.5°	1.2	1.4	1.4	1.4	1.2
40°	0.6	0.8	0.8	0.6	0.6
42.5°	0.4	0.4	0.4	0.4	0.4
45°	0.4	0.2	0.2	0.2	0.4
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.2	0.0	0.2	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.2	0.0	0.0	0.0	0.2
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320693
CATALOG NUMBER: LDSQA3D02R25B2750DE010 3LSQPHR1MB_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)