

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320784

Luminaire Tested: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320784
CATALOG NUMBER: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1320784

CATALOG NUMBER: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	94	92	90	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	92	89	88	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	90	87	85	84
7	97	91	87	84	96	91	87	84	90	86	84	89	86	83	88	85	83	88	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	86	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	178405	178405	178405
5°	173814	172621	171186
10°	146689	142177	139869
15°	88400	85922	87509
20°	29984	34621	39936
25°	5511	8627	10204
30°	1889	2108	2367
35°	547	673	736
40°	135	247	202
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 57 cd/sqm



TEST NUMBER: P1320784

CATALOG NUMBER: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	35.7
10°-20°	130.9	52.2
20°-30°	27.7	11.0
30°-40°	2.5	1.0
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.2	98.9
0°-40°	250.7	99.9
0°-60°	251.0	100.0
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1036	1036	1036	1036	1036	
5°	1005	1003	998	995	990	91
15°	496	494	482	493	491	131
25°	29	32	45	53	54	21
35°	3	3	3	4	4	2
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320784

CATALOG NUMBER: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1035.9	1035.9	1035.9	1035.9	1035.9
1°	1036.1	1035.0	1033.5	1035.7	1034.2
2°	1033.9	1031.3	1029.2	1031.3	1030.7
3°	1027.4	1025.3	1023.8	1024.9	1024.9
4°	1017.7	1015.3	1014.0	1014.2	1011.0
5°	1005.4	1003.4	998.5	995.4	990.2
6°	987.2	982.4	976.4	971.4	964.7
7°	962.5	955.2	946.5	937.9	929.4
8°	922.9	919.5	907.8	901.9	893.5
9°	885.7	877.3	864.7	855.2	850.7
10°	838.8	826.2	813.0	805.4	799.8
11°	783.1	770.4	759.8	748.7	740.1
12°	717.8	707.0	694.8	687.5	677.3
13°	640.3	638.8	625.2	622.8	621.5
14°	573.9	567.8	554.4	558.1	559.0
15°	495.8	494.0	481.9	493.2	490.8
17.5°	310.5	311.2	318.8	336.5	342.1
20°	163.6	168.6	188.9	210.3	217.9
22.5°	66.2	77.3	98.0	112.5	122.3
25°	29.0	32.5	45.4	53.4	53.7
27.5°	16.4	16.7	21.9	22.7	23.2
30°	9.5	9.7	10.6	11.3	11.9
32.5°	5.2	5.6	5.8	6.7	6.7
35°	2.6	3.2	3.2	3.9	3.5
37.5°	1.5	1.7	1.9	1.9	1.7
40°	0.6	0.9	1.1	1.1	0.9
42.5°	0.2	0.4	0.4	0.4	0.6
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320784
CATALOG NUMBER: LDSQA3D02R30B2750DE010 3LSQPHR1MMS_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)