

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1323563

Luminaire Tested: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1323563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 631.0 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1323563
CATALOG NUMBER: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1323563

CATALOG NUMBER: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90
6	103	97	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	90	88	87	86
9	97	91	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	84
10	95	90	87	84	95	90	86	84	89	86	84	88	86	84	88	85	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	973695	973695	973695
5°	792778	795354	793815
10°	369818	373123	368419
15°	116125	117106	116393
20°	46002	47835	44554
25°	18585	22480	17920
30°	7438	10222	7040
35°	2208	4520	2102
40°	674	1686	562
45°	122	365	122
50°	0	134	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 365 cd/sqm



TEST NUMBER: P1323563

CATALOG NUMBER: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.0	56.1
10°-20°	211.7	33.6
20°-30°	53.4	8.5
30°-40°	10.9	1.7
40°-50°	1.0	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.1	98.1
0°-40°	630.0	99.8
0°-60°	631.0	100.0
0°-90°	631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	631.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5654	5654	5654	5654	5654	
5°	4586	4577	4601	4589	4592	353
15°	651	657	657	647	653	212
25°	98	107	118	105	94	50
35°	10	14	22	14	10	9
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1323563

CATALOG NUMBER: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5653.7	5653.7	5653.7	5653.7	5653.7
1°	5602.8	5621.8	5611.8	5619.8	5610.8
2°	5481.5	5507.0	5499.0	5496.5	5503.5
3°	5267.9	5297.4	5296.4	5288.9	5276.9
4°	4976.5	4964.5	4983.0	4981.0	4960.5
5°	4585.7	4577.2	4600.6	4589.2	4591.7
6°	4107.5	4144.5	4136.5	4137.5	4147.0
7°	3594.0	3613.9	3630.9	3644.9	3625.4
8°	3122.3	3117.3	3118.8	3134.8	3080.9
9°	2594.3	2625.2	2605.3	2573.3	2593.8
10°	2114.7	2133.6	2133.6	2105.7	2106.7
11°	1685.9	1701.4	1690.4	1697.4	1653.5
12°	1359.0	1320.6	1311.6	1318.6	1318.1
13°	1037.6	1040.1	1037.6	1037.1	1032.1
14°	813.5	826.5	821.0	807.5	801.5
15°	651.3	656.8	656.8	647.3	652.8
17.5°	391.3	397.8	399.3	392.8	392.8
20°	251.0	254.0	261.0	251.5	243.1
22.5°	154.7	161.2	173.2	159.2	152.2
25°	97.8	106.8	118.3	104.8	94.3
27.5°	61.4	68.9	78.9	65.9	59.4
30°	37.4	42.4	51.4	41.4	35.4
32.5°	21.0	25.0	32.4	24.0	20.0
35°	10.5	14.0	21.5	13.5	10.0
37.5°	6.0	7.5	13.5	6.5	5.5
40°	3.0	4.0	7.5	4.0	2.5
42.5°	1.0	2.0	3.0	2.0	1.0
45°	0.5	1.0	1.5	1.0	0.5
47.5°	0.0	0.0	0.5	0.0	0.0
50°	0.0	0.0	0.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1323563
CATALOG NUMBER: LDSQA3D05R159030D2WDE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)