

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320870

Luminaire Tested: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 234.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320870
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1320870

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	132766	132766	132766
5°	130490	130214	129937
10°	119600	115998	113182
15°	85637	82909	81892
20°	39716	41072	42520
25°	9425	13397	13986
30°	2764	3162	3560
35°	631	1009	925
40°	135	270	180
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 57 cd/sqm



TEST NUMBER: P1320870

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	29.6
10°-20°	123.7	52.9
20°-30°	37.2	15.9
30°-40°	3.6	1.5
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.2	98.4
0°-40°	233.7	99.9
0°-60°	234.0	100.0
0°-90°	234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	234.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	771	771	771	771	771	
5°	755	755	753	752	752	70
15°	480	477	465	463	459	127
25°	50	55	70	74	74	32
35°	3	4	5	5	4	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320870

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	770.9	770.9	770.9	770.9	770.9
1°	770.5	770.5	770.1	770.1	769.3
2°	768.7	768.9	768.1	767.9	767.3
3°	765.9	765.3	765.3	764.9	764.5
4°	761.5	760.3	759.9	760.1	759.3
5°	754.8	754.6	753.2	752.2	751.6
6°	747.6	746.2	743.1	740.5	739.9
7°	736.7	733.7	731.0	725.6	724.8
8°	723.4	718.5	712.9	705.2	704.8
9°	707.1	699.2	691.3	681.1	677.4
10°	683.9	676.6	663.3	654.2	647.2
11°	655.1	646.0	630.5	619.6	613.7
12°	622.4	613.9	595.8	585.9	577.7
13°	580.5	573.4	556.5	545.6	539.2
14°	531.9	526.7	510.5	505.7	503.5
15°	480.3	476.7	465.0	463.0	459.3
17.5°	353.5	347.5	340.8	342.0	343.2
20°	216.7	225.1	224.1	228.6	232.0
22.5°	108.0	118.9	131.6	139.3	143.1
25°	49.6	54.6	70.5	73.6	73.6
27.5°	25.0	26.2	33.3	33.9	35.5
30°	13.9	14.9	15.9	17.7	17.9
32.5°	7.1	8.3	8.7	9.7	9.3
35°	3.0	4.0	4.8	5.2	4.4
37.5°	1.4	1.8	2.6	2.4	1.8
40°	0.6	0.8	1.2	1.0	0.8
42.5°	0.4	0.4	0.6	0.4	0.4
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320870
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)