

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1323614

Luminaire Tested: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1323614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 579.0 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1323614
CATALOG NUMBER: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ···· 90°-270°



TEST NUMBER: P1323614

CATALOG NUMBER: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100															
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	99	99	99	99	99	99	99	99	99	99	99	97															
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	96	96	96	96	96	96	96	96	96	96	96	94															
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	93	93	93	93	93	93	93	93	93	93	93	93	93	92															
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	90	90	90	90	90	90	90	90	90	90	90	90	90	89															
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	88	88	88	88	88	88	88	88	88	88	88	88	88	87															
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	85	85	85	85	85	85	85	85	85	85	85	85	85	84															
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	83	83	83	83	83	83	83	83	83	83	83	83	83	82															
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	81	81	81	81	81	81	81	81	81	81	81	81	81	80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	79	79	79	79	79	79	79	79	79	79	79	79	79	78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	77	77	77	77	77	77	77	77	77	77	77	77	77	76															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	411543	411543	411543
5°	400944	398178	394894
10°	338357	327969	322653
15°	203902	198214	201851
20°	69168	79871	92133
25°	12713	19915	23525
30°	4375	4872	5469
35°	1261	1577	1682
40°	337	562	450
45°	122	122	122
50°	134	0	134
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 141 cd/sqm



TEST NUMBER: P1323614

CATALOG NUMBER: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.6	35.7
10°-20°	302.0	52.2
20°-30°	63.9	11.0
30°-40°	5.9	1.0
40°-50°	0.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.5	98.9
0°-40°	578.4	99.9
0°-60°	579.0	100.0
0°-90°	579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2390	2390	2390	2390	2390	
5°	2319	2315	2303	2296	2284	209
15°	1144	1140	1112	1138	1132	302
25°	67	75	105	123	124	49
35°	6	8	8	9	8	5
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1323614

CATALOG NUMBER: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2389.6	2389.6	2389.6	2389.6	2389.6
1°	2390.1	2387.6	2384.1	2389.1	2385.6
2°	2385.1	2379.1	2374.1	2379.1	2377.6
3°	2370.1	2365.1	2361.6	2364.1	2364.1
4°	2347.6	2342.1	2339.1	2339.6	2332.2
5°	2319.2	2314.7	2303.2	2296.2	2284.2
6°	2277.2	2266.3	2252.3	2240.8	2225.3
7°	2220.3	2203.4	2183.4	2163.4	2144.0
8°	2129.0	2121.0	2094.0	2080.6	2061.1
9°	2043.1	2023.7	1994.7	1972.7	1962.3
10°	1934.8	1905.9	1875.4	1857.9	1845.0
11°	1806.5	1777.1	1752.6	1727.1	1707.2
12°	1655.8	1630.8	1602.9	1585.9	1562.4
13°	1477.1	1473.6	1442.1	1436.6	1433.6
14°	1323.8	1309.8	1278.9	1287.4	1289.4
15°	1143.6	1139.6	1111.7	1137.6	1132.1
17.5°	716.3	717.8	735.3	776.2	789.2
20°	377.4	388.9	435.8	485.2	502.7
22.5°	152.7	178.2	226.1	259.6	282.0
25°	66.9	74.9	104.8	123.3	123.8
27.5°	37.9	38.4	50.4	52.4	53.4
30°	22.0	22.5	24.5	26.0	27.5
32.5°	12.0	13.0	13.5	15.5	15.5
35°	6.0	7.5	7.5	9.0	8.0
37.5°	3.5	4.0	4.5	4.5	4.0
40°	1.5	2.0	2.5	2.5	2.0
42.5°	0.5	1.0	1.0	1.0	1.5
45°	0.5	0.5	0.5	0.5	0.5
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.0	0.0	0.0	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1323614
CATALOG NUMBER: LDSQA3D05R309030D2WDE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)