

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320873

Luminaire Tested: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320873  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , 3LSQPHR1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 235.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320873  
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1320873

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	133335	133335	133335
5°	131061	130767	130490
10°	120107	116505	113672
15°	86011	83265	82249
20°	39881	41255	42703
25°	9463	13454	14043
30°	2784	3182	3580
35°	631	1030	946
40°	135	270	180
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 57 cd/sqm



TEST NUMBER: P1320873

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.5	29.6
10°-20°	124.3	52.9
20°-30°	37.4	15.9
30°-40°	3.6	1.5
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.2	98.4
0°-40°	234.7	99.9
0°-60°	235.0	100.0
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	758	758	756	755	755	70
15°	482	479	467	465	461	127
25°	50	55	71	74	74	32
35°	3	4	5	5	4	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320873

CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	774.2	774.2	774.2	774.2	774.2
1°	773.8	773.8	773.4	773.4	772.6
2°	772.0	772.2	771.4	771.2	770.6
3°	769.2	768.6	768.6	768.2	767.8
4°	764.7	763.5	763.1	763.3	762.5
5°	758.1	757.8	756.4	755.4	754.8
6°	750.8	749.3	746.3	743.7	743.1
7°	739.8	736.8	734.2	728.7	727.9
8°	726.5	721.6	715.9	708.3	707.9
9°	710.1	702.2	694.3	684.0	680.3
10°	686.8	679.5	666.2	657.0	650.0
11°	657.9	648.7	633.2	622.2	616.4
12°	625.1	616.6	598.3	588.4	580.1
13°	583.0	575.9	558.9	547.9	541.5
14°	534.2	528.9	512.7	507.9	505.6
15°	482.4	478.7	467.0	465.0	461.3
17.5°	355.0	349.0	342.3	343.5	344.7
20°	217.6	226.1	225.1	229.5	233.0
22.5°	108.5	119.4	132.2	139.9	143.7
25°	49.8	54.9	70.8	73.9	73.9
27.5°	25.1	26.3	33.4	34.0	35.6
30°	14.0	15.0	16.0	17.8	18.0
32.5°	7.1	8.3	8.7	9.7	9.3
35°	3.0	4.0	4.9	5.3	4.5
37.5°	1.4	1.8	2.6	2.4	1.8
40°	0.6	0.8	1.2	1.0	0.8
42.5°	0.4	0.4	0.6	0.4	0.4
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320873  
CATALOG NUMBER: LDSQA3D02R35B2750DE010 3LSQPHR1MW\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)