

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320911

Luminaire Tested: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-64)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , 3LSQCA30R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 235.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 2.53 / 0.42 / 1.24
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320911
CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1320911

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	56	51	62	56	51	61	55	51	59	54	51	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	4788	4788	4788	4788	4788
5°	21593	13761	4287	1642	1210
10°	49526	26599	3025	595	455
15°	74332	37746	1872	321	285
20°	101773	47322	1100	183	220
25°	114092	55298	570	152	190
30°	124112	44625	239	119	199
35°	133379	22833	84	168	252
40°	133431	9105	45	180	315
45°	85197	3044	97	292	438
50°	44235	375	161	375	536
55°	3813	60	180	480	661
60°	138	69	207	551	758
65°	163	82	326	571	815
70°	101	101	403	604	806
75°	133	133	399	665	932
80°	198	198	595	595	793
85°	0	395	1186	790	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 85197 cd/sqm



TEST NUMBER: P1320911

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.4	2.3
10°-20°	31.8	13.5
20°-30°	69.7	29.6
30°-40°	79.4	33.8
40°-50°	41.9	17.8
50°-60°	4.9	2.1
60°-70°	0.9	0.4
70°-80°	0.7	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	106.9	45.5
0°-40°	186.2	79.2
0°-60°	233.1	99.2
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	28	28	28	28	28	
5°	125	80	25	10	7	17
15°	417	212	10	2	2	123
25°	600	291	3	1	1	277
35°	634	109	0	1	1	393
45°	350	12	0	1	2	282
55°	13	0	1	2	2	39
65°	0	0	1	1	2	0
75°	0	0	1	1	1	0
85°	0	0	1	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1320911

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	67.5°
0°	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8
2.5°	62.0	62.0	61.8	60.0	59.8	59.6	56.4	55.6	51.8	49.3	37.5
5°	124.9	122.1	122.0	118.8	113.4	106.3	101.7	94.3	87.2	79.6	46.3
7.5°	199.0	201.4	194.8	191.5	179.6	171.0	157.9	146.4	130.3	115.2	53.4
10°	283.2	279.1	272.5	265.9	253.0	237.7	218.3	197.8	174.6	152.1	57.4
12.5°	349.0	343.6	339.6	330.7	318.0	298.3	275.1	247.7	216.9	184.5	57.2
15°	416.9	411.5	402.6	394.7	375.8	353.7	328.5	292.4	254.6	211.7	53.0
17.5°	491.6	484.6	474.7	462.6	444.3	419.9	387.9	343.8	290.4	234.0	45.5
20°	555.3	551.2	541.2	526.9	509.1	485.2	448.3	399.4	334.3	258.2	36.1
22.5°	597.0	593.3	586.5	574.0	560.5	535.1	501.3	447.7	371.0	280.2	27.4
25°	600.4	598.8	597.0	592.9	584.7	566.7	533.7	475.9	393.9	291.0	20.3
27.5°	598.6	598.0	597.6	595.5	590.1	572.2	538.5	480.1	390.9	274.3	14.9
30°	624.1	622.3	621.3	614.1	600.0	572.4	528.3	457.6	347.4	224.4	10.7
32.5°	637.0	636.6	635.6	628.6	608.8	572.8	511.2	403.4	275.5	162.1	7.3
35°	634.4	632.4	628.8	615.9	588.3	543.2	456.0	322.2	198.8	108.6	4.8
37.5°	625.6	621.1	614.1	590.9	554.1	492.6	369.8	237.1	135.3	70.3	2.8
40°	593.5	587.3	576.4	548.0	499.7	406.0	273.5	160.3	88.8	40.5	0.8
42.5°	510.2	502.3	494.4	462.6	407.4	302.7	179.9	99.1	50.6	22.2	0.2
45°	349.8	339.8	328.9	305.9	261.6	183.3	107.1	55.8	26.2	12.5	0.2
47.5°	242.9	238.3	219.3	189.9	145.6	97.1	55.4	27.4	13.9	5.8	0.2
50°	165.1	159.9	137.6	109.2	77.5	46.5	25.4	13.7	6.2	1.4	0.2
52.5°	86.6	80.2	66.1	50.4	31.4	19.5	11.1	6.0	1.8	0.2	0.2
55°	12.7	11.7	9.5	7.7	7.0	5.4	3.2	1.4	0.2	0.2	0.4
57.5°	0.4	0.4	0.4	0.4	0.6	0.6	0.4	0.2	0.2	0.2	0.4
60°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
62.5°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
65°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
67.5°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4	0.6
70°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6
72.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6
75°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6
77.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6
80°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.2	0.2	0.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320911

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_3000K

CANDELA DISTRIBUTION (continued):

	90°	112.5°	135°	157.5°	180°
0°	27.8	27.8	27.8	27.8	27.8
2.5°	27.4	20.3	15.7	13.5	13.3
5°	24.8	14.5	9.5	7.3	7.0
7.5°	21.1	10.1	5.6	4.0	3.8
10°	17.3	7.0	3.4	2.8	2.6
12.5°	13.7	4.6	2.4	2.2	2.0
15°	10.5	3.0	1.8	1.6	1.6
17.5°	7.9	2.0	1.4	1.4	1.4
20°	6.0	1.4	1.0	1.2	1.2
22.5°	4.2	1.0	0.8	1.0	1.0
25°	3.0	0.8	0.8	1.0	1.0
27.5°	2.0	0.6	0.6	0.8	1.0
30°	1.2	0.4	0.6	0.8	1.0
32.5°	0.6	0.4	0.6	1.0	1.0
35°	0.4	0.6	0.8	1.0	1.2
37.5°	0.2	0.6	0.8	1.2	1.2
40°	0.2	0.6	0.8	1.2	1.4
42.5°	0.4	0.8	1.0	1.4	1.6
45°	0.4	0.8	1.2	1.6	1.8
47.5°	0.4	0.8	1.4	1.8	1.8
50°	0.6	1.0	1.4	1.8	2.0
52.5°	0.6	1.0	1.4	2.0	2.2
55°	0.6	1.0	1.6	2.0	2.2
57.5°	0.6	1.2	1.6	2.0	2.2
60°	0.6	1.0	1.6	2.0	2.2
62.5°	0.8	1.0	1.4	2.0	2.0
65°	0.8	1.0	1.4	2.0	2.0
67.5°	0.8	1.0	1.4	1.8	1.8
70°	0.8	1.0	1.2	1.6	1.6
72.5°	0.8	1.0	1.2	1.4	1.6
75°	0.6	0.8	1.0	1.2	1.4
77.5°	0.6	0.8	0.8	1.2	1.2
80°	0.6	0.6	0.6	0.8	0.8
82.5°	0.6	0.6	0.4	0.6	0.6
85°	0.6	0.4	0.4	0.4	0.4
87.5°	0.4	0.4	0.2	0.2	0.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)