

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320913

Luminaire Tested: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-64)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 80CRI , 3LSQCA30R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 239.9 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 2.53 / 0.41 / 1.24
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320913
CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1320913

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74
4	92	83	77	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67
5	86	76	69	64	84	75	68	64	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	4891	4891	4891	4891	4891
5°	22060	14055	4391	1677	1227
10°	50593	27176	3078	595	455
15°	75919	38548	1926	321	285
20°	103954	48330	1118	183	220
25°	116524	56476	570	152	190
30°	126737	45580	239	119	199
35°	136218	23337	84	168	252
40°	136264	9308	45	180	315
45°	86999	3118	97	292	438
50°	45173	375	161	375	536
55°	3903	60	180	480	661
60°	138	69	207	551	758
65°	163	82	326	571	815
70°	101	101	403	604	806
75°	133	133	399	665	932
80°	198	198	595	595	793
85°	0	395	1186	790	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 86999 cd/sqm



TEST NUMBER: P1320913

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.5	2.3
10°-20°	32.5	13.5
20°-30°	71.1	29.6
30°-40°	81.0	33.8
40°-50°	42.8	17.8
50°-60°	5.0	2.1
60°-70°	0.9	0.4
70°-80°	0.7	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.2	45.5
0°-40°	190.2	79.3
0°-60°	238.0	99.2
0°-90°	239.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	239.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	28	28	28	28	28	
5°	128	81	25	10	7	17
15°	426	216	11	2	2	125
25°	613	297	3	1	1	283
35°	648	111	0	1	1	402
45°	357	13	0	1	2	288
55°	13	0	1	2	2	40
65°	0	0	1	1	2	0
75°	0	0	1	1	1	0
85°	0	0	1	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1320913

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	67.5°
0°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
2.5°	63.3	63.3	63.1	61.3	61.1	60.9	57.6	56.8	52.9	50.3	38.3
5°	127.6	124.7	124.5	121.3	115.8	108.5	103.9	96.4	89.0	81.3	47.3
7.5°	203.2	205.7	199.0	195.5	183.4	174.6	161.3	149.5	133.1	117.6	54.6
10°	289.3	285.0	278.3	271.6	258.4	242.8	222.9	202.0	178.3	155.4	58.6
12.5°	356.4	350.9	346.9	337.7	324.8	304.7	280.9	252.9	221.5	188.4	58.4
15°	425.8	420.3	411.2	403.1	383.8	361.3	335.5	298.6	260.0	216.2	54.2
17.5°	502.0	494.9	484.8	472.4	453.8	428.8	396.2	351.1	296.6	238.9	46.5
20°	567.2	562.9	552.7	538.1	519.9	495.5	457.8	407.9	341.4	263.7	36.9
22.5°	609.7	605.9	599.0	586.2	572.4	546.5	512.0	457.2	378.9	286.2	28.0
25°	613.2	611.6	609.7	605.5	597.2	578.7	545.0	486.0	402.2	297.2	20.7
27.5°	611.4	610.8	610.4	608.1	602.6	584.4	549.9	490.3	399.2	280.1	15.2
30°	637.3	635.5	634.5	627.2	612.8	584.6	539.6	467.4	354.8	229.2	11.0
32.5°	650.5	650.1	649.1	642.0	621.7	585.0	522.1	412.0	281.3	165.5	7.5
35°	647.9	645.9	642.2	629.0	600.8	554.8	465.7	329.0	203.0	111.0	4.9
37.5°	639.0	634.3	627.2	603.5	565.9	503.1	377.7	242.2	138.1	71.8	2.8
40°	606.1	599.8	588.7	559.6	510.4	414.6	279.3	163.7	90.7	41.4	0.8
42.5°	521.1	513.0	504.9	472.4	416.0	309.1	183.8	101.2	51.7	22.7	0.2
45°	357.2	347.1	335.9	312.4	267.1	187.2	109.3	57.0	26.8	12.8	0.2
47.5°	248.1	243.4	223.9	193.9	148.7	99.2	56.6	28.0	14.2	5.9	0.2
50°	168.6	163.3	140.6	111.6	79.1	47.5	26.0	14.0	6.3	1.4	0.2
52.5°	88.4	81.9	67.5	51.5	32.0	19.9	11.4	6.1	1.8	0.2	0.2
55°	13.0	12.0	9.7	7.9	7.1	5.5	3.2	1.4	0.2	0.2	0.4
57.5°	0.4	0.4	0.4	0.4	0.6	0.6	0.4	0.2	0.2	0.2	0.4
60°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
62.5°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
65°	0.4	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4
67.5°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.4	0.6
70°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6
72.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6
75°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6
77.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6
80°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.2	0.2	0.6
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320913

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCA30R 1MW_4000K

CANDELA DISTRIBUTION (continued):

	90°	112.5°	135°	157.5°	180°
0°	28.4	28.4	28.4	28.4	28.4
2.5°	28.0	20.7	16.0	13.8	13.6
5°	25.4	14.8	9.7	7.5	7.1
7.5°	21.5	10.3	5.7	4.1	3.9
10°	17.6	7.1	3.4	2.8	2.6
12.5°	14.0	4.7	2.4	2.2	2.0
15°	10.8	3.0	1.8	1.6	1.6
17.5°	8.1	2.0	1.4	1.4	1.4
20°	6.1	1.4	1.0	1.2	1.2
22.5°	4.3	1.0	0.8	1.0	1.0
25°	3.0	0.8	0.8	1.0	1.0
27.5°	2.0	0.6	0.6	0.8	1.0
30°	1.2	0.4	0.6	0.8	1.0
32.5°	0.6	0.4	0.6	1.0	1.0
35°	0.4	0.6	0.8	1.0	1.2
37.5°	0.2	0.6	0.8	1.2	1.2
40°	0.2	0.6	0.8	1.2	1.4
42.5°	0.4	0.8	1.0	1.4	1.6
45°	0.4	0.8	1.2	1.6	1.8
47.5°	0.4	0.8	1.4	1.8	1.8
50°	0.6	1.0	1.4	1.8	2.0
52.5°	0.6	1.0	1.4	2.0	2.2
55°	0.6	1.0	1.6	2.0	2.2
57.5°	0.6	1.2	1.6	2.0	2.2
60°	0.6	1.0	1.6	2.0	2.2
62.5°	0.8	1.0	1.4	2.0	2.0
65°	0.8	1.0	1.4	2.0	2.0
67.5°	0.8	1.0	1.4	1.8	1.8
70°	0.8	1.0	1.2	1.6	1.6
72.5°	0.8	1.0	1.2	1.4	1.6
75°	0.6	0.8	1.0	1.2	1.4
77.5°	0.6	0.8	0.8	1.2	1.2
80°	0.6	0.6	0.6	0.8	0.8
82.5°	0.6	0.6	0.4	0.6	0.6
85°	0.6	0.4	0.4	0.4	0.4
87.5°	0.4	0.4	0.2	0.2	0.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)