

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320932

Luminaire Tested: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 80CRI , 3LSQCDR1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 290.0 lumens  
Efficiency: N/A  
Efficacy: 100.0 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320932  
CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1320932

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	92	92	92	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	88	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	82	80	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	80	77	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	75	72	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	118765	118765	118765
5°	117749	118475	119046
10°	114389	114179	115963
15°	99508	101113	102343
20°	65319	66584	67445
25°	23278	24646	23164
30°	5071	6861	5111
35°	1640	2838	1598
40°	495	877	450
45°	49	292	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 292 cd/sqm



TEST NUMBER: P1320932

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.5	22.2
10°-20°	150.2	51.8
20°-30°	67.4	23.2
30°-40°	7.3	2.5
40°-50°	0.7	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<b>0°-30°</b>	<b>282.0</b>	<b>97.3</b>
<b>0°-40°</b>	<b>289.3</b>	<b>99.8</b>
<b>0°-60°</b>	<b>290.0</b>	<b>100.0</b>
<b>0°-90°</b>	<b>290.0</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
<b>0°-180°</b>	<b>290.0</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	690	690	690	690	690	
5°	681	683	685	686	689	64
15°	558	562	567	570	574	148
25°	122	126	130	132	122	65
35°	8	9	14	9	8	6
45°	0	0	1	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320932

CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	689.6	689.6	689.6	689.6	689.6
1°	688.2	689.6	690.9	689.8	691.3
2°	687.6	689.2	691.1	690.0	691.3
3°	686.0	688.0	690.0	689.4	690.6
4°	683.7	685.3	688.4	688.4	690.2
5°	681.1	682.9	685.3	686.4	688.6
6°	678.2	679.2	681.1	683.1	686.2
7°	674.5	674.5	676.8	678.8	682.9
8°	669.4	669.0	670.6	673.3	677.0
9°	663.1	661.7	662.9	666.8	672.3
10°	654.1	652.9	652.9	657.8	663.1
11°	642.5	642.0	642.3	646.9	654.1
12°	626.7	627.1	627.1	632.4	641.2
13°	609.0	608.8	610.6	616.5	622.4
14°	587.3	588.5	590.4	595.7	601.8
15°	558.1	562.2	567.1	570.4	574.0
17.5°	469.3	473.4	480.1	482.8	483.6
20°	356.4	362.3	363.3	368.6	368.0
22.5°	238.9	238.5	239.3	240.0	240.2
25°	122.5	126.2	129.7	131.9	121.9
27.5°	53.3	59.6	64.1	58.2	53.9
30°	25.5	29.0	34.5	29.2	25.7
32.5°	13.9	16.1	21.9	15.9	13.7
35°	7.8	9.0	13.5	8.8	7.6
37.5°	4.5	4.9	7.4	4.9	4.3
40°	2.2	2.9	3.9	2.9	2.0
42.5°	0.8	1.4	2.0	1.4	0.8
45°	0.2	0.4	1.2	0.4	0.2
47.5°	0.0	0.0	0.6	0.0	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320932  
CATALOG NUMBER: LDSQA3D02R40B2750DE010 3LSQCDR1MB\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)