

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320966

Luminaire Tested: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1320966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , 3LSQCA45R 1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 241.1 lumens  
Efficiency: N/A  
Efficacy: 83.1 lumens/watt  
Spacing Criteria (0/90/45): 3.81 / 0.83 / 1.83  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320966  
CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1320966

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	35	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	2394	2394	2394	2394	2394
5°	2853	2645	2368	2196	2196
10°	4564	3095	2221	2081	2081
15°	11358	4154	2033	1961	2033
20°	29929	6213	1759	1869	1979
25°	60086	9197	1520	1748	1938
30°	88595	12310	1233	1710	1989
35°	111745	14444	1051	1682	2060
40°	119222	14591	944	1754	2203
45°	123874	12178	877	1900	2387
50°	123677	8493	857	2036	2679
55°	105121	3753	901	2282	2943
60°	70646	758	896	2549	3376
65°	18746	326	897	2771	3831
70°	504	403	906	3021	4330
75°	399	399	932	3194	4924
80°	397	595	992	3372	5554
85°	395	790	1581	3557	5533

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 10°  
 Vertical Angle: 47.5°  
 Luminance: 127053 cd/sqm



TEST NUMBER: P1320966

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.4	0.6
10°-20°	6.8	2.8
20°-30°	28.0	11.6
30°-40°	59.1	24.5
40°-50°	72.9	30.2
50°-60°	54.7	22.7
60°-70°	14.1	5.8
70°-80°	2.9	1.2
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<b>0°-30°</b>	<b>36.2</b>	<b>15.0</b>
<b>0°-40°</b>	<b>95.3</b>	<b>39.5</b>
<b>0°-60°</b>	<b>222.9</b>	<b>92.5</b>
<b>0°-90°</b>	<b>241.1</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
<b>0°-180°</b>	<b>241.1</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	14	14	14	14	14	
5°	16	15	14	13	13	2
15°	64	23	11	11	11	23
25°	316	48	8	9	10	147
35°	532	69	5	8	10	324
45°	509	50	4	8	10	389
55°	350	12	3	8	10	302
65°	46	1	2	7	9	66
75°	1	1	1	5	7	1
85°	0	0	1	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1320966  
 CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9
2.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.5	14.3	13.9	13.5
5°	16.5	16.3	16.3	16.3	16.1	15.9	15.9	15.3	14.5	13.7	13.1
7.5°	19.5	19.5	19.3	18.9	18.7	18.3	17.9	16.3	14.5	13.3	12.5
10°	26.1	25.7	25.1	24.7	23.7	22.3	21.3	17.7	14.3	12.7	12.1
12.5°	39.0	39.8	37.8	35.8	33.1	30.5	27.3	20.1	14.3	12.1	11.5
15°	63.7	65.1	61.3	57.4	50.6	44.2	38.2	23.3	13.9	11.4	10.8
17.5°	104.1	105.9	99.6	90.2	79.7	66.9	56.0	27.7	13.5	10.6	10.2
20°	163.3	163.1	150.7	139.0	118.7	100.0	79.5	33.9	12.9	9.6	9.6
22.5°	236.0	236.8	221.6	200.5	171.7	141.6	108.9	41.0	12.1	8.8	9.0
25°	316.2	309.5	291.5	265.8	229.0	187.4	144.4	48.4	11.4	8.0	8.4
27.5°	383.1	376.6	356.0	325.6	286.0	236.6	180.4	55.8	10.4	7.2	7.8
30°	445.5	437.1	412.4	378.0	330.8	277.4	214.3	61.9	9.2	6.2	7.2
32.5°	496.8	489.3	461.2	421.2	369.8	312.4	242.9	66.7	8.0	5.6	6.8
35°	531.5	523.7	497.8	453.8	397.9	337.9	266.2	68.7	7.0	5.0	6.6
37.5°	539.4	535.3	516.7	475.5	417.2	354.3	281.2	68.1	5.8	4.6	6.2
40°	530.3	531.3	522.5	488.3	427.5	361.2	287.3	64.9	4.8	4.2	6.0
42.5°	518.5	521.1	520.5	493.5	431.9	361.6	284.8	58.5	3.8	3.8	5.8
45°	508.6	511.2	514.8	491.3	428.9	356.4	276.6	50.0	2.8	3.6	5.8
47.5°	490.5	493.3	498.4	473.7	413.8	343.1	261.9	40.6	2.0	3.4	5.6
50°	461.6	463.0	461.6	433.9	384.7	321.6	238.0	31.7	1.4	3.2	5.6
52.5°	431.9	429.1	417.6	382.5	338.5	287.5	207.9	22.5	1.0	3.0	5.4
55°	350.1	345.7	337.1	315.6	290.5	245.7	168.1	12.5	1.0	3.0	5.2
57.5°	243.9	246.3	249.3	244.9	233.4	193.6	127.6	5.6	1.0	2.8	5.2
60°	205.1	203.1	203.3	200.5	181.4	141.2	87.8	2.2	1.0	2.6	5.0
62.5°	122.5	123.9	126.4	127.0	108.1	78.9	46.0	1.0	1.0	2.4	4.8
65°	46.0	48.2	42.2	36.6	29.1	21.3	10.8	0.8	1.2	2.2	4.4
67.5°	1.4	1.6	2.0	1.8	1.8	1.6	1.2	0.8	1.2	2.0	4.2
70°	1.0	1.0	1.0	1.0	1.0	0.8	0.8	0.8	1.0	1.8	3.8
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.0	1.6	3.4
75°	0.6	0.8	0.6	0.6	0.6	0.6	0.6	0.6	1.0	1.4	2.8
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.8	1.2	2.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.6	0.8	1.0	2.0
82.5°	0.4	0.4	0.4	0.2	0.4	0.4	0.4	0.4	0.8	0.8	1.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6	0.8	1.0
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320966

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MMS\_3000K

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	13.9	13.9	13.9
2.5°	13.1	13.1	13.1
5°	12.7	12.7	12.7
7.5°	12.3	12.3	12.3
10°	11.9	11.9	11.9
12.5°	11.5	11.5	11.7
15°	11.0	11.4	11.4
17.5°	10.6	11.0	11.2
20°	10.2	10.6	10.8
22.5°	9.6	10.2	10.6
25°	9.2	10.0	10.2
27.5°	8.8	9.8	10.2
30°	8.6	9.6	10.0
32.5°	8.2	9.4	9.8
35°	8.0	9.4	9.8
37.5°	8.0	9.2	9.8
40°	7.8	9.2	9.8
42.5°	7.8	9.2	9.8
45°	7.8	9.2	9.8
47.5°	7.6	9.2	10.0
50°	7.6	9.4	10.0
52.5°	7.6	9.4	10.0
55°	7.6	9.4	9.8
57.5°	7.4	9.2	9.8
60°	7.4	9.2	9.8
62.5°	7.0	9.0	9.6
65°	6.8	8.8	9.4
67.5°	6.4	8.6	9.0
70°	6.0	8.0	8.6
72.5°	5.4	7.6	8.2
75°	4.8	7.0	7.4
77.5°	4.2	6.2	6.6
80°	3.4	5.2	5.6
82.5°	2.6	4.0	4.2
85°	1.8	2.6	2.8
87.5°	0.8	1.2	1.4
90°	0.0	0.0	0.0

(END OF REPORT)