

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320970

Luminaire Tested: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , 3LSQCA45R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 3.81 / 0.83 / 1.83
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320970
CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1320970

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	40	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	2428	2428	2428	2428	2428
5°	2887	2680	2403	2230	2230
10°	4617	3130	2256	2116	2116
15°	11500	4208	2050	1979	2050
20°	30295	6286	1778	1888	1998
25°	60847	9311	1539	1767	1957
30°	89688	12469	1233	1730	2009
35°	113133	14633	1051	1703	2081
40°	120706	14771	944	1776	2226
45°	125409	12324	877	1924	2411
50°	125204	8601	857	2063	2706
55°	106413	3813	901	2312	2973
60°	71541	758	896	2583	3410
65°	18990	326	897	2812	3871
70°	504	403	906	3021	4381
75°	399	399	932	3194	4991
80°	397	595	992	3372	5554
85°	395	790	1581	3557	5533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 10°
 Vertical Angle: 47.5°
 Luminance: 128634 cd/sqm



TEST NUMBER: P1320970

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.4	0.6
10°-20°	6.9	2.8
20°-30°	28.4	11.6
30°-40°	59.8	24.5
40°-50°	73.8	30.2
50°-60°	55.3	22.7
60°-70°	14.2	5.8
70°-80°	2.9	1.2
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	36.7	15.0
0°-40°	96.5	39.6
0°-60°	225.6	92.5
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	14	14	14	14	14	
5°	17	16	14	13	13	2
15°	64	24	12	11	12	24
25°	320	49	8	9	10	149
35°	538	70	5	8	10	328
45°	515	51	4	8	10	394
55°	354	13	3	8	10	306
65°	47	1	2	7	10	67
75°	1	1	1	5	8	1
85°	0	0	1	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1320970

CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1
2.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.7	14.5	14.1	13.7
5°	16.7	16.5	16.5	16.5	16.3	16.1	16.1	15.5	14.7	13.9	13.3
7.5°	19.8	19.8	19.6	19.2	19.0	18.5	18.1	16.5	14.7	13.5	12.7
10°	26.4	26.0	25.4	25.0	24.0	22.6	21.6	17.9	14.5	12.9	12.3
12.5°	39.5	40.3	38.3	36.3	33.5	30.8	27.6	20.4	14.5	12.3	11.7
15°	64.5	65.9	62.1	58.1	51.2	44.8	38.7	23.6	14.1	11.5	10.9
17.5°	105.4	107.3	100.8	91.3	80.6	67.7	56.7	28.0	13.7	10.7	10.3
20°	165.3	165.1	152.6	140.7	120.2	101.2	80.4	34.3	13.1	9.7	9.7
22.5°	238.9	239.7	224.4	203.0	173.8	143.3	110.3	41.5	12.3	8.9	9.1
25°	320.2	313.3	295.2	269.2	231.9	189.7	146.2	49.0	11.5	8.1	8.5
27.5°	387.9	381.2	360.5	329.6	289.5	239.5	182.7	56.5	10.5	7.3	7.9
30°	451.0	442.5	417.5	382.7	334.9	280.8	216.9	62.7	9.3	6.2	7.3
32.5°	503.0	495.4	466.9	426.4	374.4	316.3	246.0	67.5	8.1	5.6	6.9
35°	538.1	530.2	504.0	459.5	402.8	342.1	269.6	69.6	7.1	5.0	6.7
37.5°	546.2	541.9	523.2	481.4	422.4	358.7	284.7	69.0	5.8	4.6	6.2
40°	536.9	537.9	529.0	494.4	432.9	365.7	290.9	65.7	4.8	4.2	6.0
42.5°	525.0	527.6	527.0	499.6	437.3	366.1	288.3	59.3	3.8	3.8	5.8
45°	514.9	517.5	521.2	497.4	434.3	360.9	280.0	50.6	2.8	3.6	5.8
47.5°	496.6	499.4	504.6	479.6	418.9	347.4	265.1	41.1	2.0	3.4	5.6
50°	467.3	468.7	467.3	439.3	389.5	325.6	240.9	32.1	1.4	3.2	5.6
52.5°	437.3	434.5	422.8	387.3	342.7	291.1	210.5	22.8	1.0	3.0	5.4
55°	354.4	350.0	341.3	319.6	294.2	248.8	170.2	12.7	1.0	3.0	5.2
57.5°	247.0	249.4	252.4	248.0	236.3	196.0	129.2	5.6	1.0	2.8	5.2
60°	207.7	205.6	205.8	203.0	183.7	142.9	88.9	2.2	1.0	2.6	5.0
62.5°	124.0	125.4	128.0	128.6	109.5	79.8	46.6	1.0	1.0	2.4	4.8
65°	46.6	48.8	42.7	37.1	29.4	21.6	10.9	0.8	1.2	2.2	4.4
67.5°	1.4	1.6	2.0	1.8	1.8	1.6	1.2	0.8	1.2	2.0	4.2
70°	1.0	1.0	1.0	1.0	1.0	0.8	0.8	0.8	1.0	1.8	3.8
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.0	1.6	3.4
75°	0.6	0.8	0.6	0.6	0.6	0.6	0.6	0.6	1.0	1.4	2.8
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.8	1.2	2.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.6	0.8	1.0	2.0
82.5°	0.4	0.4	0.4	0.2	0.4	0.4	0.4	0.4	0.8	0.8	1.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6	0.8	1.0
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320970
CATALOG NUMBER: LDSQA3D02R45B2750DE010 3LSQCA45R 1MW_2700K

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	14.1	14.1	14.1
2.5°	13.3	13.3	13.3
5°	12.9	12.9	12.9
7.5°	12.5	12.5	12.5
10°	12.1	12.1	12.1
12.5°	11.7	11.7	11.9
15°	11.1	11.5	11.5
17.5°	10.7	11.1	11.3
20°	10.3	10.7	10.9
22.5°	9.7	10.3	10.7
25°	9.3	10.1	10.3
27.5°	8.9	9.9	10.3
30°	8.7	9.7	10.1
32.5°	8.3	9.5	9.9
35°	8.1	9.5	9.9
37.5°	8.1	9.3	9.9
40°	7.9	9.3	9.9
42.5°	7.9	9.3	9.9
45°	7.9	9.3	9.9
47.5°	7.7	9.3	10.1
50°	7.7	9.5	10.1
52.5°	7.7	9.5	10.1
55°	7.7	9.5	9.9
57.5°	7.5	9.3	9.9
60°	7.5	9.3	9.9
62.5°	7.1	9.1	9.7
65°	6.9	8.9	9.5
67.5°	6.5	8.7	9.1
70°	6.0	8.1	8.7
72.5°	5.4	7.7	8.3
75°	4.8	7.1	7.5
77.5°	4.2	6.2	6.7
80°	3.4	5.2	5.6
82.5°	2.6	4.0	4.2
85°	1.8	2.6	2.8
87.5°	0.8	1.2	1.4
90°	0.0	0.0	0.0

(END OF REPORT)