

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1321118

Luminaire Tested: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1321118  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 80CRI , 3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 254.0 lumens  
Efficiency: N/A  
Efficacy: 87.6 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 2.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1321118  
CATALOG NUMBER: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1321118

CATALOG NUMBER: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	49359	49359	49359
5°	46747	46989	47058
10°	48529	48459	48739
15°	49335	49264	49620
20°	43656	43656	43730
25°	37416	36295	36599
30°	29929	28836	29293
35°	18565	18943	18523
40°	8161	8970	8386
45°	97	2923	244
50°	0	322	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 2923 cd/sqm



TEST NUMBER: P1321118

CATALOG NUMBER: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.2	10.3
10°-20°	75.9	29.9
20°-30°	88.1	34.7
30°-40°	55.5	21.8
40°-50°	8.3	3.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<b>0°-30°</b>	<b>190.1</b>	<b>74.9</b>
<b>0°-40°</b>	<b>245.6</b>	<b>96.7</b>
<b>0°-60°</b>	<b>254.0</b>	<b>100.0</b>
<b>0°-90°</b>	<b>254.0</b>	<b>100.0</b>
90°-120°	0.0	0.0
90°-150°	0.0	0.0
<b>90°-180°</b>	<b>0.0</b>	<b>0.0</b>
<b>0°-180°</b>	<b>254.0</b>	<b>100.0</b>

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	287	287	287	287	287	
5°	270	271	272	272	272	26
15°	277	276	276	278	278	76
25°	197	195	191	192	193	89
35°	88	88	90	88	88	55
45°	0	4	12	5	1	5
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1321118

CATALOG NUMBER: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	286.6	286.6	286.6	286.6	286.6
1°	284.4	285.2	285.2	285.4	285.2
2°	280.5	281.8	281.8	282.4	282.0
3°	276.7	277.7	277.9	278.7	278.5
4°	272.4	274.1	274.7	275.1	274.9
5°	270.4	271.4	271.8	272.4	272.2
6°	269.6	270.4	270.8	271.4	271.4
7°	270.2	270.8	271.4	271.8	271.4
8°	272.0	272.6	272.6	273.5	272.8
9°	274.7	274.9	274.9	275.9	275.3
10°	277.5	277.1	277.1	278.5	278.7
11°	279.9	279.5	279.3	280.7	281.2
12°	281.4	280.5	280.5	282.4	282.6
13°	281.6	280.5	280.5	282.4	283.0
14°	279.9	278.7	278.9	280.9	281.6
15°	276.7	275.7	276.3	278.1	278.3
17.5°	261.3	260.7	261.1	262.3	262.5
20°	238.2	237.8	238.2	238.2	238.6
22.5°	215.3	214.3	212.3	213.5	213.7
25°	196.9	194.7	191.0	191.8	192.6
27.5°	176.6	173.8	169.9	171.0	171.2
30°	150.5	149.1	145.0	146.0	147.3
32.5°	116.3	120.1	117.7	117.5	117.7
35°	88.3	88.5	90.1	88.3	88.1
37.5°	61.8	62.0	63.2	61.2	61.4
40°	36.3	38.9	39.9	39.1	37.3
42.5°	11.3	20.1	22.7	19.6	12.6
45°	0.4	3.8	12.0	5.1	1.0
47.5°	0.0	0.2	5.7	0.4	0.0
50°	0.0	0.0	1.2	0.0	0.0
52.5°	0.0	0.0	0.2	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1321118

CATALOG NUMBER: LDSQA3D02R60B2750DE010 3LSQCDR1MMS\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)