

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1323467

Luminaire Tested: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1323467  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R309030D2WDE010 3LSQPHR1MB  
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
3LSQPHR1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 378.0 lumens  
Efficiency: N/A  
Efficacy: 52.5 lumens/watt  
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1323467  
CATALOG NUMBER: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1323467  
 CATALOG NUMBER: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99		97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96		94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93		92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90		89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88		87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85		84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83		82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81		80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79		78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77		76

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	268667	268667	268667
5°	261758	259943	257817
10°	220890	214122	210642
15°	133117	129409	131780
20°	45159	52142	60151
25°	8304	12998	15354
30°	2844	3182	3560
35°	820	1030	1093
40°	225	360	292
45°	73	73	73
50°	80	0	80
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 85 cd/sqm



TEST NUMBER: P1323467

CATALOG NUMBER: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.9	35.7
10°-20°	197.2	52.2
20°-30°	41.7	11.0
30°-40°	3.8	1.0
40°-50°	0.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.8	98.9
0°-40°	377.6	99.9
0°-60°	378.0	100.0
0°-90°	378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	378.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1560	1560	1560	1560	1560	
5°	1514	1511	1504	1499	1491	137
15°	747	744	726	743	739	197
25°	44	49	68	80	81	32
35°	4	5	5	6	5	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1323467

CATALOG NUMBER: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1560.0	1560.0	1560.0	1560.0	1560.0
1°	1560.3	1558.7	1556.4	1559.7	1557.4
2°	1557.1	1553.2	1549.9	1553.2	1552.2
3°	1547.3	1544.1	1541.8	1543.4	1543.4
4°	1532.6	1529.1	1527.1	1527.4	1522.5
5°	1514.1	1511.1	1503.6	1499.1	1491.3
6°	1486.7	1479.5	1470.4	1462.9	1452.8
7°	1449.5	1438.5	1425.4	1412.4	1399.7
8°	1389.9	1384.7	1367.1	1358.3	1345.6
9°	1333.9	1321.1	1302.2	1287.9	1281.1
10°	1263.1	1244.2	1224.4	1213.0	1204.5
11°	1179.4	1160.2	1144.2	1127.6	1114.5
12°	1081.0	1064.7	1046.4	1035.3	1020.0
13°	964.3	962.0	941.5	937.9	935.9
14°	864.3	855.1	834.9	840.5	841.8
15°	746.6	744.0	725.8	742.7	739.1
17.5°	467.6	468.6	480.0	506.8	515.2
20°	246.4	253.9	284.5	316.8	328.2
22.5°	99.7	116.3	147.6	169.5	184.1
25°	43.7	48.9	68.4	80.5	80.8
27.5°	24.8	25.1	32.9	34.2	34.9
30°	14.3	14.7	16.0	16.9	17.9
32.5°	7.8	8.5	8.8	10.1	10.1
35°	3.9	4.9	4.9	5.9	5.2
37.5°	2.3	2.6	2.9	2.9	2.6
40°	1.0	1.3	1.6	1.6	1.3
42.5°	0.3	0.7	0.7	0.7	1.0
45°	0.3	0.3	0.3	0.3	0.3
47.5°	0.3	0.3	0.0	0.3	0.3
50°	0.3	0.0	0.0	0.0	0.3
52.5°	0.3	0.0	0.0	0.0	0.3
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1323467

CATALOG NUMBER: LDSQA3D02R309030D2WDE010 3LSQPHR1MB

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)