

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1323597

Luminaire Tested: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1323597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 560.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1323597
CATALOG NUMBER: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270°



TEST NUMBER: P1323597

CATALOG NUMBER: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	522592	522592	522592
5°	473572	477876	480210
10°	356002	358538	360199
15°	176283	171023	182417
20°	49778	50602	51152
25°	8627	16323	10242
30°	3381	3480	3580
35°	1051	1156	1156
40°	337	450	337
45°	244	122	244
50°	134	0	134
55°	150	0	150
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 244 cd/sqm



TEST NUMBER: P1323597

CATALOG NUMBER: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.0	43.0
10°-20°	271.8	48.5
20°-30°	42.2	7.5
30°-40°	4.3	0.8
40°-50°	0.6	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.1	99.1
0°-40°	559.3	99.9
0°-60°	560.0	100.0
0°-90°	560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3034	3034	3034	3034	3034	
5°	2739	2744	2764	2775	2778	239
15°	989	982	959	1002	1023	271
25°	45	67	86	65	54	38
35°	5	6	6	6	6	4
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1323597

CATALOG NUMBER: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3034.4	3034.4	3034.4	3034.4	3034.4
1°	3021.9	3025.9	3021.4	3026.4	3025.9
2°	2990.4	2994.4	2988.9	2991.9	2991.9
3°	2926.0	2934.5	2939.5	2943.0	2946.0
4°	2841.1	2850.6	2858.1	2867.1	2867.1
5°	2739.3	2744.3	2764.2	2775.2	2777.7
6°	2617.9	2637.9	2652.9	2674.9	2661.4
7°	2496.6	2513.1	2534.1	2537.5	2547.0
8°	2358.8	2376.3	2395.7	2392.2	2384.3
9°	2191.0	2216.5	2239.5	2232.0	2241.9
10°	2035.7	2051.2	2050.2	2042.7	2059.7
11°	1855.5	1859.0	1839.5	1870.0	1851.5
12°	1641.8	1644.8	1619.8	1649.8	1668.7
13°	1437.0	1430.1	1395.6	1435.0	1459.0
14°	1201.4	1203.9	1159.9	1236.3	1230.3
15°	988.7	981.7	959.2	1002.1	1023.1
17.5°	526.8	531.3	525.8	547.3	560.7
20°	271.6	279.1	276.1	285.1	279.1
22.5°	140.8	151.3	154.3	147.3	128.3
25°	45.4	67.4	85.9	65.4	53.9
27.5°	27.5	27.0	41.9	29.0	29.5
30°	17.0	16.5	17.5	17.5	18.0
32.5°	9.5	10.0	9.5	10.5	10.0
35°	5.0	5.5	5.5	6.0	5.5
37.5°	3.0	3.5	3.5	3.5	3.0
40°	1.5	2.0	2.0	1.5	1.5
42.5°	1.0	1.0	1.0	1.0	1.0
45°	1.0	0.5	0.5	0.5	1.0
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.5	0.0	0.5	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.5	0.0	0.0	0.0	0.5
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1323597
CATALOG NUMBER: LDSQA3D05R259030D2WDE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)