

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1323744

Luminaire Tested: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1323744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R259030D2WDE010 3LSQPHR1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 751.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1323744
CATALOG NUMBER: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1323744

CATALOG NUMBER: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	700826	700826	700826
5°	635094	640868	643997
10°	477438	480831	483052
15°	236405	229345	244643
20°	66767	67867	68600
25°	11573	21891	13739
30°	4534	4653	4793
35°	1409	1556	1556
40°	450	607	450
45°	317	170	317
50°	188	0	188
55°	210	0	210
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 317 cd/sqm



TEST NUMBER: P1323744

CATALOG NUMBER: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.3	43.0
10°-20°	364.6	48.5
20°-30°	56.5	7.5
30°-40°	5.7	0.8
40°-50°	0.8	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.4	99.1
0°-40°	750.1	99.9
0°-60°	751.0	100.0
0°-90°	751.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	751.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4069	4069	4069	4069	4069	
5°	3674	3680	3707	3722	3725	320
15°	1326	1316	1286	1344	1372	363
25°	61	90	115	88	72	51
35°	7	7	7	8	7	5
45°	1	1	1	1	1	1
55°	1	0	0	0	1	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1323744

CATALOG NUMBER: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4069.3	4069.3	4069.3	4069.3	4069.3
1°	4052.6	4057.9	4051.9	4058.6	4057.9
2°	4010.4	4015.7	4008.4	4012.4	4012.4
3°	3924.0	3935.4	3942.1	3946.8	3950.8
4°	3810.2	3822.9	3832.9	3845.0	3845.0
5°	3673.6	3680.3	3707.0	3721.8	3725.1
6°	3510.8	3537.6	3557.7	3587.2	3569.1
7°	3348.1	3370.2	3398.3	3403.0	3415.8
8°	3163.3	3186.7	3212.9	3208.2	3197.5
9°	2938.3	2972.5	3003.3	2993.2	3006.6
10°	2730.1	2750.8	2749.5	2739.4	2762.2
11°	2488.3	2493.0	2466.9	2507.7	2483.0
12°	2201.7	2205.7	2172.3	2212.4	2237.9
13°	1927.2	1917.8	1871.6	1924.5	1956.6
14°	1611.1	1614.5	1555.5	1658.0	1650.0
15°	1325.9	1316.5	1286.3	1343.9	1372.1
17.5°	706.5	712.5	705.1	733.9	752.0
20°	364.3	374.3	370.3	382.4	374.3
22.5°	188.8	202.9	206.9	197.5	172.1
25°	60.9	90.4	115.2	87.7	72.3
27.5°	36.8	36.2	56.2	38.8	39.5
30°	22.8	22.1	23.4	23.4	24.1
32.5°	12.7	13.4	12.7	14.1	13.4
35°	6.7	7.4	7.4	8.0	7.4
37.5°	4.0	4.7	4.7	4.7	4.0
40°	2.0	2.7	2.7	2.0	2.0
42.5°	1.3	1.3	1.3	1.3	1.3
45°	1.3	0.7	0.7	0.7	1.3
47.5°	0.7	0.7	0.0	0.7	0.7
50°	0.7	0.7	0.0	0.7	0.7
52.5°	0.7	0.0	0.0	0.0	0.7
55°	0.7	0.0	0.0	0.0	0.7
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1323744
CATALOG NUMBER: LDSQA3D09R259030D2WDE010 3LSQPHR1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)