

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324706

Luminaire Tested: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1324706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1324706

CATALOG NUMBER: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1324706

CATALOG NUMBER: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	96	95
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94	93	92
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	86	85	84
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	81	80	79
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	76	75
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	75	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	344394	344394	344394
5°	336011	336425	338293
10°	286977	285631	283952
15°	177086	175017	175659
20°	66932	67299	67225
25°	20599	22575	21511
30°	8293	10540	8611
35°	2439	4478	2523
40°	989	1799	989
45°	195	585	195
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 585 cd/sqm

TEST NUMBER: P1324706

CATALOG NUMBER: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.4	34.2
10°-20°	261.1	50.6
20°-30°	64.8	12.6
30°-40°	12.2	2.4
40°-50°	1.5	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.3	97.3
0°-40°	514.4	99.7
0°-60°	516.0	100.0
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2000	2000	2000	2000	2000	
5°	1944	1943	1946	1949	1957	177
15°	993	984	982	989	985	262
25°	108	116	119	118	113	62
35°	12	15	21	16	12	10
45°	1	1	2	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1324706

CATALOG NUMBER: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1999.7	1999.7	1999.7	1999.7	1999.7
1°	2000.5	1998.9	1998.9	1996.5	2000.9
2°	1993.3	1991.7	1994.5	1992.5	1998.1
3°	1982.5	1980.5	1984.5	1985.7	1988.5
4°	1966.4	1964.8	1969.2	1971.7	1979.3
5°	1943.6	1942.8	1946.0	1949.2	1956.8
6°	1912.3	1911.1	1913.1	1917.1	1921.9
7°	1866.9	1864.5	1866.1	1866.9	1868.1
8°	1809.5	1805.9	1803.9	1808.3	1810.7
9°	1735.7	1731.7	1727.3	1725.6	1731.3
10°	1641.0	1634.9	1633.3	1629.3	1623.7
11°	1531.0	1526.2	1525.0	1517.8	1514.6
12°	1405.0	1402.6	1405.4	1401.0	1399.4
13°	1284.2	1269.0	1266.9	1258.5	1254.1
14°	1141.3	1127.3	1126.9	1122.5	1128.5
15°	993.2	983.6	981.6	989.2	985.2
17.5°	633.3	639.7	638.1	634.1	627.3
20°	365.2	360.8	367.2	368.8	366.8
22.5°	194.6	196.2	197.4	202.3	205.5
25°	108.4	115.6	118.8	118.4	113.2
27.5°	67.4	71.8	77.9	73.8	69.4
30°	41.7	45.3	53.0	45.7	43.3
32.5°	22.5	28.5	34.1	28.5	23.3
35°	11.6	15.2	21.3	15.7	12.0
37.5°	7.6	8.8	13.6	8.8	7.6
40°	4.4	5.6	8.0	5.6	4.4
42.5°	2.0	3.2	4.4	3.2	2.0
45°	0.8	1.2	2.4	1.6	0.8
47.5°	0.0	0.4	1.2	0.4	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1324706

CATALOG NUMBER: LDSQA3D05R30W2N902750DE010 3LSQCDR1MMS_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)