

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324800

Luminaire Tested: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1324800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1324800
CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1324800
 CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	92	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	89	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	87	86	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	84	83	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	82	81	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	80	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	78	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	76	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	342396	342396	342396
5°	334057	334472	336322
10°	285298	283969	282308
15°	176069	174001	174643
20°	66547	66914	66841
25°	20466	22442	21378
30°	8253	10480	8571
35°	2439	4436	2523
40°	989	1799	989
45°	195	585	195
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 585 cd/sqm



TEST NUMBER: P1324800

CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.4	34.2
10°-20°	259.6	50.6
20°-30°	64.4	12.6
30°-40°	12.1	2.4
40°-50°	1.5	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	499.4	97.3
0°-40°	511.5	99.7
0°-60°	513.0	100.0
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1988	1988	1988	1988	1988	
5°	1932	1932	1935	1938	1945	175
15°	988	978	976	984	980	261
25°	108	115	118	118	112	62
35°	12	15	21	16	12	10
45°	1	1	2	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1324800

CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1988.1	1988.1	1988.1	1988.1	1988.1
1°	1988.9	1987.3	1987.3	1984.9	1989.3
2°	1981.7	1980.1	1982.9	1980.9	1986.5
3°	1971.0	1969.0	1973.0	1974.2	1976.9
4°	1955.0	1953.4	1957.8	1960.2	1967.8
5°	1932.3	1931.5	1934.7	1937.8	1945.4
6°	1901.1	1899.9	1901.9	1905.9	1910.7
7°	1856.1	1853.7	1855.3	1856.1	1857.3
8°	1799.0	1795.4	1793.4	1797.8	1800.2
9°	1725.6	1721.6	1717.2	1715.6	1721.2
10°	1631.4	1625.4	1623.8	1619.9	1614.3
11°	1522.1	1517.3	1516.1	1508.9	1505.7
12°	1396.8	1394.4	1397.2	1392.8	1391.2
13°	1276.7	1261.6	1259.6	1251.2	1246.8
14°	1134.7	1120.7	1120.3	1115.9	1121.9
15°	987.5	977.9	975.9	983.5	979.5
17.5°	629.6	636.0	634.4	630.4	623.6
20°	363.1	358.7	365.1	366.7	364.7
22.5°	193.5	195.1	196.3	201.1	204.3
25°	107.7	114.9	118.1	117.7	112.5
27.5°	67.0	71.4	77.4	73.4	69.0
30°	41.5	45.1	52.7	45.5	43.1
32.5°	22.3	28.3	33.9	28.3	23.1
35°	11.6	15.2	21.1	15.6	12.0
37.5°	7.6	8.8	13.6	8.8	7.6
40°	4.4	5.6	8.0	5.6	4.4
42.5°	2.0	3.2	4.4	3.2	2.0
45°	0.8	1.2	2.4	1.6	0.8
47.5°	0.0	0.4	1.2	0.4	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1324800
CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQCDR1MMS_6500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)