

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325336

Luminaire Tested: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1325336  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 90CRI ,  
3LSQCDR1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 566.0 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1325336  
CATALOG NUMBER: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1325336

CATALOG NUMBER: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	86	86	86	85
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	81	81	81	81	80
5	96	88	83	80	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	77	74	79	76	73	73	73	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	69	69	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	66	66	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	63	63	63	62
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	151263	151263	151263
5°	148297	148020	147605
10°	142492	141512	141582
15°	130799	129587	129444
20°	116856	115610	116197
25°	91840	94519	91080
30°	49140	55046	49299
35°	16042	18754	15117
40°	3979	4969	3799
45°	487	1754	487
50°	322	536	322
55°	360	360	360
60°	276	276	276
65°	326	326	326
70°	201	201	201
75°	266	266	266
80°	397	397	397
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1754 cd/sqm



TEST NUMBER: P1325336

CATALOG NUMBER: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.3	14.2
10°-20°	203.1	35.9
20°-30°	213.6	37.7
30°-40°	61.6	10.9
40°-50°	5.0	0.9
50°-60°	1.1	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	497.1	87.8
0°-40°	558.6	98.7
0°-60°	564.7	99.8
0°-90°	566.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	878	878	878	878	878	
5°	858	857	856	857	854	81
15°	734	729	727	727	726	204
25°	483	495	497	492	479	209
35°	76	79	89	76	72	59
45°	2	4	7	4	2	4
55°	1	1	1	1	1	1
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1325336

CATALOG NUMBER: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	878.3	878.3	878.3	878.3	878.3
1°	877.9	878.7	877.1	879.9	877.5
2°	875.9	876.3	875.5	877.5	874.3
3°	871.0	871.8	870.2	871.8	869.0
4°	865.4	865.4	863.8	865.0	861.4
5°	857.8	857.4	856.2	857.0	853.8
6°	849.8	849.3	847.3	847.3	844.9
7°	843.7	840.9	839.3	838.9	836.5
8°	834.1	833.3	830.1	830.1	828.5
9°	824.4	823.6	820.0	820.8	819.6
10°	814.8	812.0	809.2	809.6	809.6
11°	801.9	799.5	795.5	797.1	797.9
12°	786.7	783.9	780.2	783.5	783.1
13°	769.8	767.4	764.6	767.0	766.2
14°	752.1	748.5	746.1	747.7	746.9
15°	733.6	728.8	726.8	726.8	726.0
17.5°	681.8	679.0	677.0	675.8	678.6
20°	637.6	635.2	630.8	632.0	634.0
22.5°	582.2	581.8	579.4	577.3	579.8
25°	483.3	495.4	497.4	491.8	479.3
27.5°	351.1	379.3	389.3	376.1	353.2
30°	247.1	260.3	276.8	250.7	247.9
32.5°	149.1	152.7	167.9	149.9	145.8
35°	76.3	79.1	89.2	76.3	71.9
37.5°	35.8	37.4	41.4	35.8	33.3
40°	17.7	19.7	22.1	18.5	16.9
42.5°	7.6	10.0	12.9	9.6	6.8
45°	2.0	4.0	7.2	4.0	2.0
47.5°	1.2	1.6	4.0	1.6	1.2
50°	1.2	1.2	2.0	1.2	1.2
52.5°	1.2	1.2	1.2	1.2	1.2
55°	1.2	1.2	1.2	1.2	1.2
57.5°	1.2	1.2	1.2	1.2	1.2
60°	0.8	1.2	0.8	1.2	0.8
62.5°	0.8	0.8	0.8	0.8	0.8
65°	0.8	0.8	0.8	0.8	0.8
67.5°	0.8	0.8	0.8	0.8	0.8
70°	0.4	0.4	0.4	0.4	0.4
72.5°	0.4	0.4	0.4	0.4	0.4
75°	0.4	0.4	0.4	0.4	0.4
77.5°	0.4	0.4	0.4	0.4	0.4
80°	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.4	0.0	0.4	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325336  
CATALOG NUMBER: LDSQA3D05R50W2N902765DE010 3LSQCDR1MW\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)