

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325375

Luminaire Tested: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1325375  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,  
3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 515.0 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1325375  
CATALOG NUMBER: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1325375  
 CATALOG NUMBER: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	116664	116664	116664
5°	115329	114983	114378
10°	120877	119425	118603
15°	118871	117605	117177
20°	108279	108719	108352
25°	86861	88229	86861
30°	49856	51108	51506
35°	14213	17135	14633
40°	3642	5238	3732
45°	390	1827	292
50°	0	322	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1827 cd/sqm



TEST NUMBER: P1325375

CATALOG NUMBER: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.3	12.5
10°-20°	183.5	35.6
20°-30°	202.1	39.3
30°-40°	60.3	11.7
40°-50°	4.6	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.0	87.4
0°-40°	510.3	99.1
0°-60°	515.0	100.0
0°-90°	515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	515.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	677	677	677	677	677	
5°	667	666	665	662	662	65
15°	667	662	660	657	657	185
25°	457	457	464	464	457	200
35°	68	72	82	74	70	56
45°	2	4	8	4	1	3
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1325375  
 CATALOG NUMBER: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	677.4	677.4	677.4	677.4	677.4
1°	677.0	677.0	676.2	675.8	677.0
2°	675.0	675.0	673.1	672.7	673.8
3°	670.7	670.3	668.7	667.5	668.3
4°	667.1	666.3	665.1	663.2	663.6
5°	667.1	665.9	665.1	662.4	661.6
6°	670.3	669.5	667.9	665.1	664.4
7°	675.8	674.2	672.7	669.1	668.3
8°	681.8	680.6	677.4	673.8	672.3
9°	687.7	684.9	681.0	677.4	677.0
10°	691.2	687.3	682.9	678.6	678.2
11°	690.8	687.3	682.1	678.2	677.8
12°	689.3	684.1	679.8	675.0	675.4
13°	683.7	679.0	674.6	671.1	670.3
14°	676.2	671.9	667.9	664.4	664.7
15°	666.7	662.0	659.6	656.8	657.2
17.5°	633.1	631.9	633.1	629.9	631.1
20°	590.8	589.6	593.2	591.6	591.2
22.5°	531.9	533.5	540.2	538.2	534.6
25°	457.1	457.1	464.3	463.5	457.1
27.5°	359.9	362.6	367.0	369.0	364.2
30°	250.7	257.0	257.0	261.0	259.0
32.5°	140.0	153.4	156.6	158.6	150.7
35°	67.6	72.0	81.5	74.3	69.6
37.5°	32.4	34.4	43.9	35.6	33.2
40°	16.2	18.6	23.3	19.4	16.6
42.5°	6.7	9.9	12.3	9.9	6.7
45°	1.6	4.0	7.5	4.0	1.2
47.5°	0.0	0.4	3.6	0.8	0.0
50°	0.0	0.0	1.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325375  
CATALOG NUMBER: LDSQA3D05R55W2N902750DE010 3LSQCDR1MMS\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)