

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325426

Luminaire Tested: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1325426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 467.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1325426
CATALOG NUMBER: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1325426

CATALOG NUMBER: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	105796	105796	105796
5°	104575	104264	103711
10°	109614	108303	107551
15°	107799	106640	106266
20°	98181	98584	98254
25°	78766	80001	78766
30°	45202	46356	46714
35°	12888	15537	13266
40°	3305	4766	3395
45°	341	1656	268
50°	0	295	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1656 cd/sqm



TEST NUMBER: P1325426

CATALOG NUMBER: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	12.5
10°-20°	166.4	35.6
20°-30°	183.3	39.3
30°-40°	54.7	11.7
40°-50°	4.2	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.0	87.4
0°-40°	462.8	99.1
0°-60°	467.0	100.0
0°-90°	467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	467.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	614	614	614	614	614	
5°	605	604	603	601	600	59
15°	605	600	598	596	596	168
25°	414	414	421	420	414	181
35°	61	65	74	67	63	51
45°	1	4	7	4	1	3
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1325426

CATALOG NUMBER: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	614.3	614.3	614.3	614.3	614.3
1°	613.9	613.9	613.2	612.8	613.9
2°	612.1	612.1	610.3	610.0	611.0
3°	608.2	607.8	606.4	605.3	606.0
4°	604.9	604.2	603.1	601.4	601.7
5°	604.9	603.9	603.1	600.6	599.9
6°	607.8	607.1	605.7	603.1	602.4
7°	612.8	611.4	610.0	606.7	606.0
8°	618.2	617.1	614.3	611.0	609.6
9°	623.6	621.1	617.5	614.3	613.9
10°	626.8	623.2	619.3	615.3	615.0
11°	626.5	623.2	618.6	615.0	614.6
12°	625.0	620.4	616.4	612.1	612.5
13°	620.0	615.7	611.8	608.5	607.8
14°	613.2	609.2	605.7	602.4	602.8
15°	604.6	600.3	598.1	595.6	596.0
17.5°	574.1	573.0	574.1	571.2	572.3
20°	535.7	534.7	537.9	536.5	536.1
22.5°	482.3	483.7	489.8	488.0	484.8
25°	414.5	414.5	421.0	420.3	414.5
27.5°	326.3	328.8	332.8	334.6	330.3
30°	227.3	233.1	233.1	236.7	234.9
32.5°	126.9	139.1	142.0	143.8	136.6
35°	61.3	65.3	73.9	67.4	63.1
37.5°	29.4	31.2	39.8	32.3	30.1
40°	14.7	16.9	21.2	17.6	15.1
42.5°	6.1	9.0	11.1	9.0	6.1
45°	1.4	3.6	6.8	3.6	1.1
47.5°	0.0	0.4	3.2	0.7	0.0
50°	0.0	0.0	1.1	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325426
CATALOG NUMBER: LDSQA3D05R55W2N902765DE010 3LSQCDR1MMS_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)