

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324629

Luminaire Tested: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1324629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 450.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1324629
CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1324629

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	419930	419930	419930
5°	380545	384019	385887
10°	286085	288114	289443
15°	141658	137432	146579
20°	40009	40669	41109
25°	6936	13112	8228
30°	2705	2784	2864
35°	841	925	925
40°	270	360	270
45°	195	97	195
50°	107	0	107
55°	120	0	120
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 195 cd/sqm



TEST NUMBER: P1324629

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	43.0
10°-20°	218.4	48.5
20°-30°	33.9	7.5
30°-40°	3.4	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	446.0	99.1
0°-40°	449.5	99.9
0°-60°	450.0	100.0
0°-90°	450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	450.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2438	2438	2438	2438	2438	
5°	2201	2205	2221	2230	2232	192
15°	794	789	771	805	822	218
25°	36	54	69	53	43	31
35°	4	4	4	5	4	3
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1324629

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2438.3	2438.3	2438.3	2438.3	2438.3
1°	2428.3	2431.5	2427.9	2431.9	2431.5
2°	2403.0	2406.2	2401.8	2404.2	2404.2
3°	2351.3	2358.1	2362.1	2364.9	2367.3
4°	2283.1	2290.7	2296.7	2303.9	2303.9
5°	2201.2	2205.2	2221.3	2230.1	2232.1
6°	2103.7	2119.7	2131.8	2149.4	2138.6
7°	2006.2	2019.4	2036.3	2039.1	2046.7
8°	1895.5	1909.5	1925.1	1922.3	1915.9
9°	1760.6	1781.1	1799.6	1793.5	1801.6
10°	1635.9	1648.3	1647.5	1641.5	1655.1
11°	1491.0	1493.8	1478.2	1502.6	1487.8
12°	1319.3	1321.7	1301.6	1325.7	1340.9
13°	1154.8	1149.2	1121.5	1153.2	1172.4
14°	965.4	967.4	932.1	993.5	988.7
15°	794.5	788.8	770.8	805.3	822.1
17.5°	423.3	426.9	422.5	439.8	450.6
20°	218.3	224.3	221.9	229.1	224.3
22.5°	113.1	121.6	124.0	118.4	103.1
25°	36.5	54.2	69.0	52.6	43.3
27.5°	22.1	21.7	33.7	23.3	23.7
30°	13.6	13.2	14.0	14.0	14.4
32.5°	7.6	8.0	7.6	8.4	8.0
35°	4.0	4.4	4.4	4.8	4.4
37.5°	2.4	2.8	2.8	2.8	2.4
40°	1.2	1.6	1.6	1.2	1.2
42.5°	0.8	0.8	0.8	0.8	0.8
45°	0.8	0.4	0.4	0.4	0.8
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.4	0.0	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.4	0.0	0.0	0.0	0.4
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1324629
CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)