

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324631

Luminaire Tested: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1324631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 448.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1324631
CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1324631

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	418070	418070	418070
5°	378850	382308	384175
10°	284809	286837	288166
15°	141016	136826	145937
20°	39826	40486	40925
25°	6917	13055	8190
30°	2705	2784	2864
35°	841	925	925
40°	270	360	270
45°	195	97	195
50°	107	0	107
55°	120	0	120
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 195 cd/sqm



TEST NUMBER: P1324631

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.8	43.0
10°-20°	217.5	48.5
20°-30°	33.7	7.5
30°-40°	3.4	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.0	99.1
0°-40°	447.5	99.9
0°-60°	448.0	100.0
0°-90°	448.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2428	2428	2428	2428	2428	
5°	2191	2195	2211	2220	2222	191
15°	791	785	767	802	818	217
25°	36	54	69	52	43	31
35°	4	4	4	5	4	3
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1324631

CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2427.5	2427.5	2427.5	2427.5	2427.5
1°	2417.5	2420.7	2417.1	2421.1	2420.7
2°	2392.3	2395.5	2391.1	2393.5	2393.5
3°	2340.8	2347.6	2351.6	2354.4	2356.8
4°	2272.9	2280.5	2286.5	2293.7	2293.7
5°	2191.4	2195.4	2211.4	2220.2	2222.2
6°	2094.4	2110.3	2122.3	2139.9	2129.1
7°	1997.3	2010.5	2027.2	2030.0	2037.6
8°	1887.0	1901.0	1916.6	1913.8	1907.4
9°	1752.8	1773.2	1791.6	1785.6	1793.6
10°	1628.6	1641.0	1640.2	1634.2	1647.8
11°	1484.4	1487.2	1471.6	1496.0	1481.2
12°	1313.4	1315.8	1295.8	1319.8	1335.0
13°	1149.6	1144.0	1116.5	1148.0	1167.2
14°	961.1	963.1	927.9	989.1	984.3
15°	790.9	785.3	767.4	801.7	818.5
17.5°	421.4	425.0	420.6	437.8	448.6
20°	217.3	223.3	220.9	228.1	223.3
22.5°	112.6	121.0	123.4	117.8	102.7
25°	36.4	53.9	68.7	52.3	43.1
27.5°	22.0	21.6	33.6	23.2	23.6
30°	13.6	13.2	14.0	14.0	14.4
32.5°	7.6	8.0	7.6	8.4	8.0
35°	4.0	4.4	4.4	4.8	4.4
37.5°	2.4	2.8	2.8	2.8	2.4
40°	1.2	1.6	1.6	1.2	1.2
42.5°	0.8	0.8	0.8	0.8	0.8
45°	0.8	0.4	0.4	0.4	0.8
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.4	0.0	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.4	0.0	0.0	0.0	0.4
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1324631
CATALOG NUMBER: LDSQA3D05R25W2N902765DE010 3LSQPHR1MMS_6500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)