

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325692

Luminaire Tested: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1325692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,
3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 424.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 0.99 / 1.03
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1325692

CATALOG NUMBER: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1325692

CATALOG NUMBER: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106	111	108	106	104		104	103	101			101	99	98			97
2	108	103	98	95	105	101	97	94		98	95	92			95	92	90			92
3	102	95	90	86	100	94	89	85		91	87	84			89	86	83			87
4	96	89	83	79	95	88	82	78		85	81	77			83	79	76			81
5	91	83	77	72	90	82	76	72		80	75	71			78	74	71			77
6	86	77	71	67	85	76	71	66		75	70	66			73	69	65			72
7	82	72	66	62	80	71	66	61		70	65	61			69	64	61			68
8	78	68	61	57	76	67	61	57		66	61	57			65	60	57			64
9	74	63	57	53	72	63	57	53		62	57	53			61	56	53			60
10	70	60	54	50	69	59	53	50		58	53	49			58	53	49			57

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	70577	70577	70577
5°	67752	67389	67199
10°	65090	64531	64391
15°	63545	62654	62779
20°	60847	60261	60133
25°	56476	56628	55735
30°	51705	52401	50412
35°	42301	44320	40640
40°	24348	28372	25000
45°	341	11788	1218
50°	0	1259	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 11788 cd/sqm

TEST NUMBER: P1325692

CATALOG NUMBER: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	8.6
10°-20°	99.1	23.4
20°-30°	136.1	32.1
30°-40°	123.4	29.1
40°-50°	28.7	6.8
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.8	64.1
0°-40°	395.2	93.2
0°-60°	424.0	100.0
0°-90°	424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	424.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	410	410	410	410	410	
5°	392	391	390	389	389	37
15°	356	354	351	351	352	100
25°	297	299	298	295	293	136
35°	201	204	211	202	193	121
45°	1	16	48	21	5	17
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1325692

CATALOG NUMBER: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	409.8	409.8	409.8	409.8	409.8
1°	409.5	408.8	409.1	409.5	409.8
2°	406.2	405.5	405.5	405.9	405.9
3°	402.3	400.9	400.9	400.5	400.5
4°	396.9	395.8	395.1	394.8	394.8
5°	391.9	390.8	389.8	389.0	388.7
6°	387.6	385.8	384.4	384.0	384.4
7°	382.6	381.5	380.1	379.0	379.4
8°	379.0	377.6	375.8	375.1	375.1
9°	375.8	374.3	372.5	371.1	371.8
10°	372.2	370.7	369.0	367.9	368.2
11°	369.7	367.9	365.7	365.0	365.4
12°	366.8	364.7	362.5	362.1	362.9
13°	363.2	361.1	358.9	358.9	359.6
14°	360.0	357.5	355.3	355.3	356.4
15°	356.4	353.9	351.4	351.4	352.1
17.5°	345.7	343.5	341.0	341.0	341.3
20°	332.0	330.9	328.8	327.7	328.1
22.5°	314.8	314.8	313.7	311.9	311.2
25°	297.2	298.7	298.0	295.1	293.3
27.5°	279.0	281.5	281.8	277.5	274.3
30°	260.0	262.1	263.5	258.5	253.5
32.5°	232.0	238.4	242.0	235.2	224.8
35°	201.2	204.0	210.8	201.9	193.3
37.5°	163.5	167.1	172.8	165.7	160.6
40°	108.3	122.6	126.2	122.6	111.2
42.5°	39.1	68.8	82.8	70.3	45.9
45°	1.4	16.1	48.4	20.8	5.0
47.5°	0.0	0.4	21.9	0.7	0.0
50°	0.0	0.0	4.7	0.0	0.0
52.5°	0.0	0.0	0.4	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325692

CATALOG NUMBER: LDSQA3D05R70W2N902765DE010 3LSQCDR1MB_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)