

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324814

Luminaire Tested: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1324814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 459.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1324814
CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1324814

CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	94	92	90	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	92	89	88	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	90	87	85	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	88	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	86	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	326241	326241	326241
5°	317841	315663	313052
10°	268230	259993	255779
15°	161645	157134	160022
20°	54836	63322	73035
25°	10071	15791	18642
30°	3460	3858	4335
35°	988	1240	1325
40°	270	450	360
45°	97	97	97
50°	107	0	107
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 113 cd/sqm



TEST NUMBER: P1324814

CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.8	35.7
10°-20°	239.4	52.2
20°-30°	50.7	11.0
30°-40°	4.7	1.0
40°-50°	0.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	453.9	98.9
0°-40°	458.5	99.9
0°-60°	459.0	100.0
0°-90°	459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	459.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1894	1894	1894	1894	1894	
5°	1838	1835	1826	1820	1811	166
15°	907	903	881	902	898	239
25°	53	59	83	98	98	39
35°	5	6	6	7	6	4
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1324814

CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1894.3	1894.3	1894.3	1894.3	1894.3
1°	1894.7	1892.7	1890.0	1893.9	1891.1
2°	1890.7	1886.0	1882.0	1886.0	1884.8
3°	1878.9	1874.9	1872.2	1874.1	1874.1
4°	1861.1	1856.7	1854.3	1854.7	1848.8
5°	1838.5	1835.0	1825.9	1820.3	1810.8
6°	1805.3	1796.6	1785.5	1776.4	1764.1
7°	1760.2	1746.7	1730.9	1715.1	1699.6
8°	1687.7	1681.4	1660.0	1649.4	1633.9
9°	1619.7	1604.2	1581.3	1563.9	1555.6
10°	1533.8	1510.9	1486.7	1472.9	1462.6
11°	1432.1	1408.8	1389.4	1369.2	1353.4
12°	1312.6	1292.8	1270.7	1257.2	1238.6
13°	1170.9	1168.2	1143.2	1138.9	1136.5
14°	1049.4	1038.4	1013.8	1020.6	1022.1
15°	906.6	903.4	881.3	901.8	897.5
17.5°	567.9	569.0	582.9	615.3	625.6
20°	299.2	308.3	345.5	384.6	398.5
22.5°	121.1	141.3	179.3	205.8	223.6
25°	53.0	59.4	83.1	97.7	98.1
27.5°	30.1	30.5	40.0	41.6	42.3
30°	17.4	17.8	19.4	20.6	21.8
32.5°	9.5	10.3	10.7	12.3	12.3
35°	4.7	5.9	5.9	7.1	6.3
37.5°	2.8	3.2	3.6	3.6	3.2
40°	1.2	1.6	2.0	2.0	1.6
42.5°	0.4	0.8	0.8	0.8	1.2
45°	0.4	0.4	0.4	0.4	0.4
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.0	0.0	0.0	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1324814
CATALOG NUMBER: LDSQA3D05R30W2N902765DE010 3LSQPHR1MMS_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)