

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1324907

Luminaire Tested: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1324907  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,  
3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 466.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1324907

CATALOG NUMBER: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1324907

CATALOG NUMBER: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96 | 95 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 100 | 98  | 97  | 97  | 96  | 95  | 94  | 93 | 92 |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 94  | 97  | 95  | 93  | 95  | 93  | 92  | 91  | 90 | 89 |
| 4   | 104 | 99  | 95  | 92  | 103 | 98  | 94  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 93  | 90  | 89  | 88  | 87 | 86 |
| 5   | 101 | 95  | 91  | 88  | 100 | 95  | 91  | 88  | 93  | 90  | 87  | 92  | 89  | 87  | 90  | 88  | 86  | 85  | 84 | 83 |
| 6   | 98  | 92  | 88  | 85  | 97  | 91  | 88  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 82  | 81 | 80 |
| 7   | 96  | 89  | 85  | 82  | 94  | 89  | 85  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 79 | 78 |
| 8   | 93  | 86  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 79  | 84  | 81  | 79  | 83  | 80  | 78  | 77  | 76 | 75 |
| 9   | 90  | 84  | 80  | 77  | 89  | 83  | 79  | 77  | 82  | 79  | 76  | 82  | 79  | 76  | 81  | 78  | 76  | 75  | 74 | 73 |
| 10  | 88  | 81  | 77  | 75  | 87  | 81  | 77  | 74  | 80  | 77  | 74  | 80  | 76  | 74  | 79  | 76  | 74  | 73  | 72 | 71 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     | 45°    | 90°    |
|-----|--------|--------|--------|
| 0°  | 264413 | 264413 | 264413 |
| 5°  | 259874 | 259321 | 258768 |
| 10° | 238168 | 231016 | 225402 |
| 15° | 170542 | 165104 | 163107 |
| 20° | 79083  | 81796  | 84673  |
| 25° | 18756  | 26699  | 27839  |
| 30° | 5509   | 6304   | 7100   |
| 35° | 1261   | 2018   | 1850   |
| 40° | 270    | 540    | 360    |
| 45° | 97     | 97     | 97     |
| 50° | 107    | 0      | 107    |
| 55° | 0      | 0      | 0      |
| 60° | 0      | 0      | 0      |
| 65° | 0      | 0      | 0      |
| 70° | 0      | 0      | 0      |
| 75° | 0      | 0      | 0      |
| 80° | 0      | 0      | 0      |
| 85° | 0      | 0      | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 113 cd/sqm

TEST NUMBER: P1324907

CATALOG NUMBER: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 137.8  | 29.6      |
| 10°-20°   | 246.4  | 52.9      |
| 20°-30°   | 74.1   | 15.9      |
| 30°-40°   | 7.1    | 1.5       |
| 40°-50°   | 0.5    | 0.1       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 458.4  | 98.4      |
| 0°-40°    | 465.5  | 99.9      |
| 0°-60°    | 466.0  | 100.0     |
| 0°-90°    | 466.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 466.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1535 | 1535  | 1535 | 1535  | 1535 |      |
| 5°  | 1503 | 1503  | 1500 | 1498  | 1497 | 139  |
| 15° | 956  | 949   | 926  | 922   | 915  | 253  |
| 25° | 99   | 109   | 140  | 146   | 146  | 64   |
| 35° | 6    | 8     | 10   | 10    | 9    | 6    |
| 45° | 0    | 0     | 0    | 0     | 0    | 0    |
| 55° | 0    | 0     | 0    | 0     | 0    | 0    |
| 65° | 0    | 0     | 0    | 0     | 0    | 0    |
| 75° | 0    | 0     | 0    | 0     | 0    | 0    |
| 85° | 0    | 0     | 0    | 0     | 0    | 0    |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1324907

CATALOG NUMBER: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1535.3 | 1535.3 | 1535.3 | 1535.3 | 1535.3 |
| 1°    | 1534.5 | 1534.5 | 1533.7 | 1533.7 | 1532.1 |
| 2°    | 1530.9 | 1531.3 | 1529.7 | 1529.3 | 1528.1 |
| 3°    | 1525.3 | 1524.1 | 1524.1 | 1523.3 | 1522.5 |
| 4°    | 1516.4 | 1514.0 | 1513.2 | 1513.6 | 1512.0 |
| 5°    | 1503.2 | 1502.8 | 1500.0 | 1498.0 | 1496.8 |
| 6°    | 1488.7 | 1485.9 | 1479.9 | 1474.7 | 1473.5 |
| 7°    | 1467.1 | 1461.1 | 1455.8 | 1445.0 | 1443.4 |
| 8°    | 1440.6 | 1430.9 | 1419.7 | 1404.5 | 1403.7 |
| 9°    | 1408.1 | 1392.4 | 1376.8 | 1356.3 | 1349.1 |
| 10°   | 1361.9 | 1347.5 | 1321.0 | 1302.9 | 1288.9 |
| 11°   | 1304.5 | 1286.4 | 1255.5 | 1233.9 | 1222.2 |
| 12°   | 1239.5 | 1222.6 | 1186.5 | 1166.8 | 1150.4 |
| 13°   | 1156.0 | 1141.9 | 1108.2 | 1086.6 | 1073.7 |
| 14°   | 1059.3 | 1048.8 | 1016.7 | 1007.1 | 1002.7 |
| 15°   | 956.5  | 949.3  | 926.0  | 922.0  | 914.8  |
| 17.5° | 704.0  | 692.0  | 678.7  | 681.2  | 683.6  |
| 20°   | 431.5  | 448.4  | 446.3  | 455.2  | 462.0  |
| 22.5° | 215.1  | 236.8  | 262.1  | 277.4  | 285.0  |
| 25°   | 98.7   | 108.8  | 140.5  | 146.5  | 146.5  |
| 27.5° | 49.8   | 52.2   | 66.2   | 67.4   | 70.6   |
| 30°   | 27.7   | 29.7   | 31.7   | 35.3   | 35.7   |
| 32.5° | 14.0   | 16.5   | 17.3   | 19.3   | 18.5   |
| 35°   | 6.0    | 8.0    | 9.6    | 10.4   | 8.8    |
| 37.5° | 2.8    | 3.6    | 5.2    | 4.8    | 3.6    |
| 40°   | 1.2    | 1.6    | 2.4    | 2.0    | 1.6    |
| 42.5° | 0.8    | 0.8    | 1.2    | 0.8    | 0.8    |
| 45°   | 0.4    | 0.4    | 0.4    | 0.4    | 0.4    |
| 47.5° | 0.4    | 0.4    | 0.0    | 0.4    | 0.4    |
| 50°   | 0.4    | 0.0    | 0.0    | 0.0    | 0.4    |
| 52.5° | 0.4    | 0.0    | 0.0    | 0.0    | 0.4    |
| 55°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 57.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 60°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 62.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 65°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 67.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 70°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 72.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 75°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



TEST NUMBER: P1324907

CATALOG NUMBER: LDSQA3D05R35W2N902750DE010 3LSQPHR1MMS\_3500K

CANDELA DISTRIBUTION (continued):

|     | 0°  | 22.5° | 45° | 67.5° | 90° |
|-----|-----|-------|-----|-------|-----|
| 90° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

(END OF REPORT)