

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325272

Luminaire Tested: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1325272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 561.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1325272
CATALOG NUMBER: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1325272

CATALOG NUMBER: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	150040	150040	150040
5°	147415	147000	146585
10°	142177	140638	140918
15°	130782	129141	129498
20°	116783	115683	116343
25°	90890	94709	89902
30°	49239	54986	48364
35°	15516	18481	15180
40°	3417	4789	3237
45°	97	1461	97
50°	0	214	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1461 cd/sqm



TEST NUMBER: P1325272

CATALOG NUMBER: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.8	14.2
10°-20°	202.8	36.1
20°-30°	213.6	38.1
30°-40°	61.0	10.9
40°-50°	3.8	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.2	88.5
0°-40°	557.2	99.3
0°-60°	561.0	100.0
0°-90°	561.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	561.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	871	871	871	871	871	
5°	853	852	850	850	848	80
15°	734	729	724	726	726	204
25°	478	496	498	493	473	209
35°	74	79	88	75	72	58
45°	0	2	6	2	0	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1325272

CATALOG NUMBER: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	871.2	871.2	871.2	871.2	871.2
1°	871.6	872.0	871.2	872.0	870.0
2°	870.4	869.6	868.8	869.2	868.0
3°	866.0	865.6	864.0	864.4	862.8
4°	860.3	859.1	857.9	857.1	855.5
5°	852.7	851.9	850.3	849.5	847.9
6°	846.3	844.7	841.9	841.1	839.5
7°	837.9	837.1	833.5	832.7	831.9
8°	831.5	829.0	824.6	825.0	823.0
9°	823.0	819.8	815.4	815.4	815.8
10°	813.0	808.2	804.2	805.4	805.8
11°	799.8	796.5	790.5	793.3	793.3
12°	785.3	781.3	776.9	779.3	780.9
13°	768.5	765.2	761.2	763.6	762.8
14°	752.0	746.0	743.2	746.4	745.2
15°	733.5	728.7	724.3	725.5	726.3
17.5°	684.2	679.0	675.8	676.2	679.8
20°	637.2	635.2	631.2	632.8	634.8
22.5°	581.9	582.7	577.8	579.1	583.9
25°	478.3	496.0	498.4	492.8	473.1
27.5°	354.3	380.8	388.8	376.0	351.9
30°	247.6	254.8	276.5	252.0	243.2
32.5°	145.3	156.1	167.7	150.9	144.9
35°	73.8	79.1	87.9	74.6	72.2
37.5°	34.1	36.5	40.1	34.1	32.1
40°	15.2	18.1	21.3	17.3	14.4
42.5°	4.8	8.4	11.2	7.6	4.4
45°	0.4	2.0	6.0	2.0	0.4
47.5°	0.0	0.4	2.4	0.4	0.0
50°	0.0	0.0	0.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325272
CATALOG NUMBER: LDSQA3D05R50W2N902750DE010 3LSQCDR1MB_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)