

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1325529

Luminaire Tested: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1325529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1325529
CATALOG NUMBER: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1325529
 CATALOG NUMBER: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	84	81	78	77
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	75	72	69	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	97168	97168	97168
5°	92024	92508	92647
10°	95537	95397	95956
15°	97119	96976	97689
20°	85938	85938	86085
25°	73654	71450	72058
30°	58924	56776	57651
35°	36541	37297	36478
40°	16052	17671	16502
45°	195	5724	487
50°	0	643	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 5724 cd/sqm



TEST NUMBER: P1325529

CATALOG NUMBER: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	10.3
10°-20°	149.4	29.9
20°-30°	173.4	34.7
30°-40°	109.2	21.8
40°-50°	16.4	3.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.3	74.9
0°-40°	483.5	96.7
0°-60°	500.0	100.0
0°-90°	500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	532	534	535	536	536	51
15°	545	543	544	548	548	149
25°	388	383	376	378	379	176
35°	174	174	177	174	174	109
45°	1	8	24	10	2	11
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1325529

CATALOG NUMBER: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	564.2	564.2	564.2	564.2	564.2
1°	559.8	561.4	561.4	561.8	561.4
2°	552.3	554.6	554.6	555.8	555.0
3°	544.7	546.7	547.1	548.7	548.3
4°	536.3	539.5	540.7	541.5	541.1
5°	532.3	534.3	535.1	536.3	535.9
6°	530.7	532.3	533.1	534.3	534.3
7°	531.9	533.1	534.3	535.1	534.3
8°	535.5	536.7	536.7	538.3	537.1
9°	540.7	541.1	541.1	543.1	541.9
10°	546.3	545.5	545.5	548.3	548.7
11°	551.1	550.3	549.9	552.6	553.4
12°	553.8	552.3	552.3	555.8	556.2
13°	554.2	552.3	552.3	555.8	557.0
14°	551.1	548.7	549.1	553.0	554.2
15°	544.7	542.7	543.9	547.5	547.9
17.5°	514.4	513.2	514.0	516.4	516.8
20°	468.9	468.1	468.9	468.9	469.7
22.5°	423.9	421.9	417.9	420.3	420.7
25°	387.6	383.2	376.0	377.6	379.2
27.5°	347.7	342.1	334.5	336.5	336.9
30°	296.3	293.5	285.5	287.5	289.9
32.5°	228.9	236.5	231.7	231.3	231.7
35°	173.8	174.2	177.4	173.8	173.5
37.5°	121.6	122.0	124.4	120.4	120.8
40°	71.4	76.6	78.6	77.0	73.4
42.5°	22.3	39.5	44.7	38.7	24.7
45°	0.8	7.6	23.5	10.0	2.0
47.5°	0.0	0.4	11.2	0.8	0.0
50°	0.0	0.0	2.4	0.0	0.0
52.5°	0.0	0.0	0.4	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1325529
CATALOG NUMBER: LDSQA3D05R60W2N902765DE010 3LSQCDR1MMS_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)