

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1326137

Luminaire Tested: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1326137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 593.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1326137
CATALOG NUMBER: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1326137
 CATALOG NUMBER: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	553386	553386	553386
5°	501474	506039	508511
10°	376988	379663	381430
15°	186660	181097	193168
20°	52710	53590	54176
25°	9140	17273	10851
30°	3580	3679	3778
35°	1114	1219	1219
40°	360	472	360
45°	268	122	268
50°	134	0	134
55°	150	0	150
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 268 cd/sqm



TEST NUMBER: P1326137

CATALOG NUMBER: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.3	43.0
10°-20°	287.9	48.5
20°-30°	44.7	7.5
30°-40°	4.5	0.8
40°-50°	0.6	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	587.8	99.1
0°-40°	592.3	99.9
0°-60°	593.0	100.0
0°-90°	593.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3213	3213	3213	3213	3213	
5°	2901	2906	2927	2939	2941	253
15°	1047	1040	1016	1061	1083	287
25°	48	71	91	69	57	40
35°	5	6	6	6	6	4
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1326137

CATALOG NUMBER: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3213.2	3213.2	3213.2	3213.2	3213.2
1°	3200.0	3204.2	3199.4	3204.7	3204.2
2°	3166.7	3170.9	3165.1	3168.2	3168.2
3°	3098.4	3107.4	3112.7	3116.4	3119.6
4°	3008.6	3018.6	3026.5	3036.1	3036.1
5°	2900.7	2906.0	2927.1	2938.8	2941.4
6°	2772.2	2793.4	2809.2	2832.5	2818.2
7°	2643.7	2661.2	2683.4	2687.1	2697.1
8°	2497.8	2516.3	2536.9	2533.2	2524.8
9°	2320.1	2347.1	2371.4	2363.5	2374.1
10°	2155.7	2172.1	2171.0	2163.1	2181.1
11°	1964.8	1968.5	1947.9	1980.1	1960.6
12°	1738.5	1741.7	1715.2	1747.0	1767.1
13°	1521.7	1514.3	1477.8	1519.6	1545.0
14°	1272.2	1274.8	1228.3	1309.2	1302.8
15°	1046.9	1039.5	1015.7	1061.2	1083.4
17.5°	557.8	562.6	556.8	579.5	593.8
20°	287.6	295.6	292.4	301.9	295.6
22.5°	149.1	160.2	163.4	156.0	135.9
25°	48.1	71.4	90.9	69.3	57.1
27.5°	29.1	28.6	44.4	30.7	31.2
30°	18.0	17.4	18.5	18.5	19.0
32.5°	10.0	10.6	10.0	11.1	10.6
35°	5.3	5.8	5.8	6.3	5.8
37.5°	3.2	3.7	3.7	3.7	3.2
40°	1.6	2.1	2.1	1.6	1.6
42.5°	1.1	1.1	1.1	1.1	1.1
45°	1.1	0.5	0.5	0.5	1.1
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.5	0.0	0.5	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.5	0.0	0.0	0.0	0.5
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1326137
CATALOG NUMBER: LDSQA3D09R25W2N902750DE010 3LSQPHR1MMS_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)