

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1326212

Luminaire Tested: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1326212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 767.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1326212
CATALOG NUMBER: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1326212

CATALOG NUMBER: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	84	84	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	82	82	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80	80	80
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	78	78	78
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	634606	634606	634606
5°	585149	586463	587690
10°	454319	455981	458446
15°	224531	233963	234070
20°	75601	80678	77104
25°	31316	34775	32210
30°	12290	15452	12409
35°	3217	6307	3343
40°	1192	2518	1192
45°	146	706	146
50°	0	161	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 706 cd/sqm



TEST NUMBER: P1326212

CATALOG NUMBER: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.6	38.9
10°-20°	361.1	47.1
20°-30°	88.2	11.5
30°-40°	17.1	2.2
40°-50°	1.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.9	97.5
0°-40°	765.0	99.7
0°-60°	767.0	100.0
0°-90°	767.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3385	3389	3392	3407	3399	298
15°	1259	1289	1312	1325	1313	355
25°	165	174	183	175	170	84
35°	15	22	30	22	16	14
45°	1	2	3	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1326212

CATALOG NUMBER: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3684.8	3684.8	3684.8	3684.8	3684.8
1°	3670.7	3673.0	3673.6	3677.1	3670.1
2°	3637.1	3637.7	3639.5	3646.5	3640.1
3°	3575.3	3579.5	3580.1	3589.5	3591.2
4°	3491.2	3493.6	3498.3	3514.1	3500.0
5°	3384.7	3389.4	3392.3	3407.1	3399.4
6°	3252.9	3254.1	3260.5	3277.6	3267.0
7°	3118.7	3118.1	3118.7	3132.3	3129.3
8°	2956.9	2954.0	2963.4	2979.8	2991.0
9°	2788.0	2792.1	2798.0	2813.9	2801.0
10°	2597.9	2609.1	2607.4	2608.5	2621.5
11°	2379.1	2382.6	2383.2	2395.5	2393.8
12°	2121.9	2121.9	2141.3	2161.3	2154.9
13°	1862.4	1880.6	1867.7	1871.8	1897.7
14°	1559.9	1574.1	1591.7	1608.2	1595.3
15°	1259.3	1289.3	1312.2	1325.2	1312.8
17.5°	721.4	731.4	750.8	753.2	745.5
20°	412.5	424.9	440.2	435.4	420.7
22.5°	259.5	263.0	278.3	270.7	267.2
25°	164.8	173.6	183.0	175.4	169.5
27.5°	102.4	108.3	118.3	110.0	103.6
30°	61.8	67.1	77.7	66.5	62.4
32.5°	32.4	40.0	48.8	40.6	32.4
35°	15.3	21.8	30.0	21.8	15.9
37.5°	9.4	11.8	18.2	11.8	9.4
40°	5.3	7.6	11.2	7.6	5.3
42.5°	2.4	4.1	5.3	4.1	2.9
45°	0.6	1.8	2.9	1.8	0.6
47.5°	0.0	0.0	1.8	0.6	0.0
50°	0.0	0.0	0.6	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1326212
CATALOG NUMBER: LDSQA3D09R25W2N902765DE010 3LSQCDR1MB_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)