

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1326981

Luminaire Tested: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1326981
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 760.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1326981
CATALOG NUMBER: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1326981

CATALOG NUMBER: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	75	75	75	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	71	71	71	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	67	67	67	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	172171	172171	172171
5°	170201	169700	168783
10°	178395	176244	175019
15°	175427	173555	172931
20°	159798	160439	159890
25°	128192	130187	128192
30°	73580	75430	76006
35°	20982	25271	21592
40°	5373	7734	5508
45°	560	2704	438
50°	0	482	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 2704 cd/sqm



TEST NUMBER: P1326981

CATALOG NUMBER: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	12.5
10°-20°	270.8	35.6
20°-30°	298.3	39.3
30°-40°	89.0	11.7
40°-50°	6.8	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	664.1	87.4
0°-40°	753.1	99.1
0°-60°	760.0	100.0
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1000	1000	1000	1000	1000	
5°	984	983	982	978	976	95
15°	984	977	973	969	970	273
25°	675	675	685	684	675	295
35°	100	106	120	110	103	82
45°	2	6	11	6	2	4
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1326981

CATALOG NUMBER: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	999.7	999.7	999.7	999.7	999.7
1°	999.1	999.1	997.9	997.3	999.1
2°	996.2	996.2	993.2	992.7	994.4
3°	989.7	989.2	986.8	985.1	986.2
4°	984.5	983.3	981.6	978.7	979.2
5°	984.5	982.7	981.6	977.5	976.3
6°	989.2	988.0	985.7	981.6	980.4
7°	997.3	995.0	992.7	987.4	986.2
8°	1006.1	1004.3	999.7	994.4	992.1
9°	1014.8	1010.8	1004.9	999.7	999.1
10°	1020.1	1014.3	1007.8	1001.4	1000.8
11°	1019.5	1014.3	1006.7	1000.8	1000.2
12°	1017.2	1009.6	1003.2	996.2	996.7
13°	1009.0	1002.0	995.6	990.3	989.2
14°	997.9	991.5	985.7	980.4	981.0
15°	983.9	976.9	973.4	969.3	969.9
17.5°	934.3	932.6	934.3	929.6	931.4
20°	871.9	870.1	875.4	873.0	872.4
22.5°	784.9	787.2	797.2	794.2	789.0
25°	674.6	674.6	685.1	683.9	674.6
27.5°	531.1	535.1	541.6	544.5	537.5
30°	370.0	379.3	379.3	385.2	382.2
32.5°	206.6	226.4	231.1	234.0	222.3
35°	99.8	106.2	120.2	109.7	102.7
37.5°	47.9	50.8	64.8	52.5	49.0
40°	23.9	27.4	34.4	28.6	24.5
42.5°	9.9	14.6	18.1	14.6	9.9
45°	2.3	5.8	11.1	5.8	1.8
47.5°	0.0	0.6	5.3	1.2	0.0
50°	0.0	0.0	1.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1326981
CATALOG NUMBER: LDSQA3D09R55W2N902750DE010 3LSQCDR1MMS_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)