

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1327362

Luminaire Tested: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1327362  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-59)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
3LSQCA30R 1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 712.1 lumens  
Efficiency: N/A  
Efficacy: 57.9 lumens/watt  
Spacing Criteria (0/90/45): 2.35 / 0.49 / 1.26  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1327362  
CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|---|
| RF  | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |   |
| RC  | 80  |     |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |   |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 96  | 95  | 93  | 92  |   |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 89  | 87  | 85  | 83  |   |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 83  | 80  | 77  | 75  |   |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 75  | 71  | 79  | 74  | 70  | 77  | 73  | 70  | 77  | 73  | 70  | 68  |   |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 70  | 65  | 74  | 69  | 64  | 72  | 67  | 64  | 71  | 66  | 63  | 71  | 66  | 63  | 61  |   |
| 6   | 81  | 71  | 64  | 59  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 61  | 57  | 65  | 61  | 57  | 65  | 61  | 57  | 55  |   |
| 7   | 76  | 65  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 60  | 55  | 52  | 50  |   |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 47  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 56  | 51  | 47  | 45  |   |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 42  | 51  | 46  | 42  | 41  |   |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 43  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 47  | 42  | 39  | 47  | 42  | 39  | 37  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°      | 45°   | 90°  | 135° | 180° |
|-----|---------|-------|------|------|------|
| 0°  | 4047    | 4047  | 4047 | 4047 | 4047 |
| 5°  | 8748    | 6466  | 3838 | 2040 | 1677 |
| 10° | 38753   | 12242 | 3025 | 839  | 612  |
| 15° | 146579  | 28278 | 2104 | 374  | 250  |
| 20° | 563719  | 39862 | 1265 | 128  | 128  |
| 25° | 1071978 | 37378 | 665  | 0    | 0    |
| 30° | 1294973 | 30168 | 278  | 0    | 0    |
| 35° | 1009996 | 20541 | 147  | 0    | 0    |
| 40° | 368571  | 10117 | 157  | 0    | 157  |
| 45° | 94623   | 3044  | 170  | 0    | 341  |
| 50° | 15969   | 375   | 188  | 188  | 563  |
| 55° | 2072    | 0     | 420  | 631  | 1051 |
| 60° | 241     | 241   | 723  | 964  | 1447 |
| 65° | 285     | 285   | 1141 | 1426 | 1712 |
| 70° | 352     | 352   | 1410 | 1410 | 1762 |
| 75° | 466     | 466   | 1863 | 1397 | 1863 |
| 80° | 0       | 694   | 2083 | 1389 | 2083 |
| 85° | 0       | 1383  | 4150 | 1383 | 1383 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 94623 cd/sqm



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 3.2    | 0.5       |
| 10°-20°   | 54.6   | 7.7       |
| 20°-30°   | 302.6  | 42.5      |
| 30°-40°   | 292.3  | 41.1      |
| 40°-50°   | 50.8   | 7.1       |
| 50°-60°   | 3.7    | 0.5       |
| 60°-70°   | 2.2    | 0.3       |
| 70°-80°   | 1.8    | 0.2       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 360.4  | 50.6      |
| 0°-40°    | 652.7  | 91.7      |
| 0°-60°    | 707.2  | 99.3      |
| 0°-90°    | 712.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 712.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0°  | 24   | 24  | 24  | 24   | 24   |      |
| 5°  | 51   | 37  | 22  | 12   | 10   | 10   |
| 15° | 822  | 159 | 12  | 2    | 1    | 366  |
| 25° | 5641 | 197 | 4   | 0    | 0    | 2522 |
| 35° | 4804 | 98  | 1   | 0    | 0    | 2763 |
| 45° | 388  | 12  | 1   | 0    | 1    | 417  |
| 55° | 7    | 0   | 1   | 2    | 4    | 13   |
| 65° | 1    | 1   | 3   | 4    | 4    | 1    |
| 75° | 1    | 1   | 3   | 2    | 3    | 0    |
| 85° | 0    | 1   | 2   | 1    | 1    | 0    |
| 90° | 0    | 0   | 0   | 0    | 0    |      |



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 45°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0°    | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5   | 23.5  |
| 2.5°  | 34.6   | 33.2   | 33.9   | 33.9   | 33.9   | 33.9   | 33.9   | 32.6   | 32.6   | 33.2   | 29.8  |
| 5°    | 50.6   | 50.6   | 49.9   | 50.6   | 50.6   | 49.9   | 48.5   | 47.8   | 47.8   | 46.4   | 37.4  |
| 7.5°  | 101.1  | 99.7   | 99.7   | 98.3   | 91.4   | 89.3   | 88.0   | 84.5   | 78.3   | 76.9   | 48.5  |
| 10°   | 221.6  | 222.3  | 217.5  | 211.2  | 210.5  | 200.2  | 196.7  | 190.5  | 178.7  | 166.9  | 70.0  |
| 12.5° | 402.4  | 393.4  | 381.6  | 382.3  | 362.2  | 355.3  | 339.4  | 322.1  | 304.1  | 285.3  | 115.0 |
| 15°   | 822.1  | 796.5  | 811.7  | 774.3  | 732.1  | 684.3  | 635.8  | 574.9  | 522.9  | 467.5  | 158.6 |
| 17.5° | 1731.5 | 1756.4 | 1714.2 | 1554.2 | 1455.8 | 1340.2 | 1177.4 | 1020.2 | 885.8  | 777.8  | 193.9 |
| 20°   | 3075.8 | 3112.5 | 2969.2 | 2830.0 | 2591.0 | 2330.6 | 2059.1 | 1751.6 | 1457.2 | 1202.3 | 217.5 |
| 21°   | 3637.5 | 3615.4 | 3556.5 | 3333.5 | 3057.8 | 2755.8 | 2423.4 | 2084.0 | 1727.3 | 1396.3 | 219.6 |
| 22°   | 4180.5 | 4190.9 | 4053.8 | 3820.4 | 3533.6 | 3199.1 | 2793.2 | 2374.2 | 1989.8 | 1554.2 | 216.1 |
| 23°   | 4721.4 | 4754.7 | 4573.2 | 4354.4 | 3993.5 | 3616.0 | 3146.5 | 2694.2 | 2219.1 | 1735.0 | 209.2 |
| 24°   | 5222.2 | 5199.3 | 5076.7 | 4801.1 | 4415.3 | 3973.4 | 3485.8 | 2937.3 | 2407.5 | 1889.4 | 203.6 |
| 25°   | 5641.2 | 5638.4 | 5445.9 | 5177.9 | 4736.7 | 4247.0 | 3709.5 | 3136.1 | 2568.8 | 1994.0 | 196.7 |
| 26°   | 5984.0 | 5927.9 | 5776.3 | 5449.4 | 5013.7 | 4497.0 | 3893.1 | 3280.8 | 2659.6 | 2046.6 | 189.8 |
| 27°   | 6248.6 | 6208.4 | 6004.8 | 5664.8 | 5209.7 | 4638.3 | 4010.8 | 3352.9 | 2701.1 | 2063.9 | 180.8 |
| 28°   | 6426.6 | 6383.0 | 6166.2 | 5815.7 | 5317.8 | 4727.0 | 4073.2 | 3383.3 | 2701.1 | 2047.3 | 172.5 |
| 29°   | 6518.7 | 6459.2 | 6243.1 | 5867.7 | 5342.7 | 4737.4 | 4057.9 | 3353.6 | 2658.9 | 1996.1 | 162.8 |
| 30°   | 6511.8 | 6437.7 | 6211.2 | 5820.6 | 5268.6 | 4652.2 | 3972.7 | 3246.2 | 2563.3 | 1919.9 | 151.7 |
| 31°   | 6399.6 | 6316.5 | 6063.7 | 5661.3 | 5115.5 | 4491.5 | 3812.1 | 3102.1 | 2432.4 | 1820.8 | 140.6 |
| 32°   | 6171.7 | 6066.5 | 5819.9 | 5418.9 | 4880.0 | 4251.2 | 3578.6 | 2879.8 | 2236.4 | 1676.1 | 128.8 |
| 33°   | 5800.5 | 5694.5 | 5430.0 | 5053.9 | 4561.4 | 3946.4 | 3269.1 | 2640.9 | 2013.4 | 1503.6 | 119.1 |
| 34°   | 5335.8 | 5238.8 | 5010.9 | 4632.1 | 4159.7 | 3560.6 | 2913.1 | 2310.5 | 1782.1 | 1332.6 | 108.7 |
| 35°   | 4803.9 | 4649.4 | 4443.0 | 4143.1 | 3682.5 | 3080.0 | 2528.7 | 2003.0 | 1543.8 | 1153.2 | 97.7  |
| 36°   | 4084.2 | 4111.9 | 3893.1 | 3526.0 | 3144.4 | 2672.0 | 2142.9 | 1669.9 | 1291.0 | 982.8  | 88.0  |
| 37°   | 3446.4 | 3402.7 | 3263.5 | 2979.6 | 2647.1 | 2178.2 | 1795.9 | 1415.7 | 1086.0 | 831.1  | 77.6  |
| 38°   | 2780.1 | 2789.8 | 2653.3 | 2435.2 | 2105.5 | 1791.1 | 1445.4 | 1162.9 | 908.7  | 707.1  | 67.9  |
| 39°   | 2176.1 | 2168.5 | 2131.8 | 1929.6 | 1631.1 | 1424.7 | 1171.2 | 964.1  | 757.0  | 596.3  | 57.5  |
| 40°   | 1639.4 | 1651.8 | 1566.0 | 1444.1 | 1270.2 | 1100.5 | 932.9  | 768.8  | 626.1  | 502.8  | 45.0  |
| 42.5° | 797.2  | 816.6  | 759.8  | 728.6  | 651.7  | 585.2  | 493.8  | 403.1  | 342.8  | 296.4  | 20.1  |
| 45°   | 388.5  | 377.5  | 372.6  | 357.4  | 339.4  | 303.4  | 268.7  | 230.6  | 201.5  | 173.8  | 12.5  |
| 47.5° | 198.8  | 193.2  | 193.2  | 187.0  | 180.8  | 169.0  | 151.7  | 139.2  | 125.4  | 108.0  | 4.8   |
| 50°   | 59.6   | 58.9   | 58.2   | 58.9   | 56.8   | 58.9   | 60.3   | 60.9   | 55.4   | 54.7   | 1.4   |
| 52.5° | 23.5   | 24.2   | 23.5   | 25.6   | 25.6   | 24.9   | 25.6   | 24.9   | 24.2   | 21.5   | 0.0   |
| 55°   | 6.9    | 6.9    | 6.9    | 6.9    | 6.9    | 6.9    | 7.6    | 8.3    | 7.6    | 8.3    | 0.0   |
| 57.5° | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    | 0.0   |
| 60°   | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.0    | 0.7   |
| 62.5° | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 65°   | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 67.5° | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 70°   | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 72.5° | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 75°   | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.7    | 0.7    | 0.7   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.7   |



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 82.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.7 |
| 85°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.7 |
| 87.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.7 |
| 90°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90°  | 112.5° | 135° | 157.5° | 180° |
|-------|-------|------|--------|------|--------|------|
| 0°    | 23.5  | 23.5 | 23.5   | 23.5 | 23.5   | 23.5 |
| 2.5°  | 27.7  | 24.2 | 20.1   | 16.6 | 15.2   | 14.5 |
| 5°    | 29.8  | 22.2 | 15.2   | 11.8 | 10.4   | 9.7  |
| 7.5°  | 31.9  | 20.1 | 11.8   | 8.3  | 6.2    | 5.5  |
| 10°   | 33.2  | 17.3 | 9.0    | 4.8  | 3.5    | 3.5  |
| 12.5° | 33.2  | 13.9 | 6.2    | 2.8  | 2.1    | 2.1  |
| 15°   | 32.6  | 11.8 | 4.2    | 2.1  | 1.4    | 1.4  |
| 17.5° | 31.9  | 9.0  | 2.8    | 1.4  | 0.7    | 1.4  |
| 20°   | 29.8  | 6.9  | 1.4    | 0.7  | 0.7    | 0.7  |
| 21°   | 29.1  | 6.2  | 1.4    | 0.7  | 0.7    | 0.7  |
| 22°   | 27.7  | 5.5  | 0.7    | 0.0  | 0.7    | 0.7  |
| 23°   | 26.3  | 4.2  | 0.7    | 0.0  | 0.0    | 0.0  |
| 24°   | 24.2  | 3.5  | 0.7    | 0.0  | 0.0    | 0.0  |
| 25°   | 22.9  | 3.5  | 0.7    | 0.0  | 0.0    | 0.0  |
| 26°   | 21.5  | 2.1  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27°   | 19.4  | 1.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 28°   | 18.0  | 1.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29°   | 15.9  | 1.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°   | 13.9  | 1.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 31°   | 11.1  | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32°   | 9.0   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33°   | 6.2   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 34°   | 4.2   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°   | 3.5   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 36°   | 2.1   | 0.7  | 0.0    | 0.0  | 0.0    | 0.7  |
| 37°   | 2.1   | 0.7  | 0.0    | 0.0  | 0.0    | 0.7  |
| 38°   | 1.4   | 0.7  | 0.0    | 0.0  | 0.0    | 0.7  |
| 39°   | 0.7   | 0.7  | 0.0    | 0.0  | 0.0    | 0.7  |
| 40°   | 0.7   | 0.7  | 0.0    | 0.0  | 0.0    | 0.7  |
| 42.5° | 0.0   | 0.7  | 0.0    | 0.0  | 0.7    | 1.4  |
| 45°   | 0.0   | 0.7  | 0.0    | 0.0  | 0.7    | 1.4  |
| 47.5° | 0.0   | 0.7  | 0.0    | 0.0  | 1.4    | 1.4  |
| 50°   | 0.0   | 0.7  | 0.7    | 0.7  | 1.4    | 2.1  |
| 52.5° | 0.0   | 1.4  | 0.7    | 1.4  | 2.1    | 2.8  |
| 55°   | 0.7   | 1.4  | 1.4    | 2.1  | 2.8    | 3.5  |
| 57.5° | 0.7   | 2.1  | 2.1    | 2.8  | 3.5    | 3.5  |
| 60°   | 1.4   | 2.1  | 2.8    | 2.8  | 4.2    | 4.2  |
| 62.5° | 1.4   | 2.8  | 2.8    | 2.8  | 4.2    | 4.2  |
| 65°   | 1.4   | 2.8  | 2.8    | 3.5  | 4.2    | 4.2  |
| 67.5° | 1.4   | 2.8  | 2.8    | 2.8  | 3.5    | 4.2  |
| 70°   | 1.4   | 2.8  | 2.1    | 2.8  | 3.5    | 3.5  |
| 72.5° | 1.4   | 2.8  | 2.1    | 2.1  | 2.8    | 3.5  |
| 75°   | 1.4   | 2.8  | 2.1    | 2.1  | 2.8    | 2.8  |
| 77.5° | 1.4   | 2.1  | 2.1    | 1.4  | 2.1    | 2.1  |
| 80°   | 1.4   | 2.1  | 1.4    | 1.4  | 2.1    | 2.1  |



TEST NUMBER: P1327362

CATALOG NUMBER: LDSQA3D13R15W2N902750DE010 3LSQCA30R 1MW\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|--------|------|--------|------|
| 82.5° | 1.4   | 2.1 | 1.4    | 0.7  | 1.4    | 1.4  |
| 85°   | 1.4   | 2.1 | 1.4    | 0.7  | 0.7    | 0.7  |
| 87.5° | 1.4   | 2.1 | 0.7    | 0.0  | 0.0    | 0.7  |
| 90°   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |

(END OF REPORT)