

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1326508

Luminaire Tested: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1326508  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,  
3LSQPHR1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 687.0 lumens  
Efficiency: N/A  
Efficacy: 76.3 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1326508  
CATALOG NUMBER: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1326508

CATALOG NUMBER: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	389809	389809	389809
5°	383120	382308	381478
10°	351123	340560	332288
15°	251418	243412	240453
20°	116582	120595	124829
25°	27668	39355	41046
30°	8114	9287	10480
35°	1871	2985	2733
40°	405	809	540
45°	146	146	146
50°	161	0	161
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 170 cd/sqm



TEST NUMBER: P1326508

CATALOG NUMBER: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.2	29.6
10°-20°	363.3	52.9
20°-30°	109.3	15.9
30°-40°	10.5	1.5
40°-50°	0.7	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.8	98.4
0°-40°	686.2	99.9
0°-60°	687.0	100.0
0°-90°	687.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2263	2263	2263	2263	2263	
5°	2216	2216	2211	2208	2207	205
15°	1410	1400	1365	1359	1349	372
25°	146	160	207	216	216	94
35°	9	12	14	15	13	8
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1326508

CATALOG NUMBER: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2263.4	2263.4	2263.4	2263.4	2263.4
1°	2262.2	2262.2	2261.1	2261.1	2258.7
2°	2256.9	2257.5	2255.1	2254.6	2252.8
3°	2248.6	2246.9	2246.9	2245.7	2244.5
4°	2235.6	2232.1	2230.9	2231.5	2229.1
5°	2216.1	2215.5	2211.4	2208.4	2206.6
6°	2194.8	2190.6	2181.8	2174.1	2172.3
7°	2162.8	2154.0	2146.3	2130.3	2127.9
8°	2123.8	2109.6	2093.0	2070.5	2069.3
9°	2075.8	2052.8	2029.7	1999.5	1988.9
10°	2007.8	1986.5	1947.4	1920.8	1900.1
11°	1923.2	1896.5	1851.0	1819.0	1801.9
12°	1827.3	1802.5	1749.2	1720.2	1695.9
13°	1704.2	1683.5	1633.8	1601.9	1582.9
14°	1561.6	1546.2	1498.9	1484.7	1478.2
15°	1410.1	1399.5	1365.2	1359.2	1348.6
17.5°	1037.9	1020.2	1000.6	1004.2	1007.7
20°	636.1	661.0	658.0	671.0	681.1
22.5°	317.2	349.1	386.4	408.9	420.1
25°	145.6	160.4	207.1	216.0	216.0
27.5°	73.4	76.9	97.6	99.4	104.1
30°	40.8	43.8	46.7	52.1	52.7
32.5°	20.7	24.3	25.4	28.4	27.2
35°	8.9	11.8	14.2	15.4	13.0
37.5°	4.1	5.3	7.7	7.1	5.3
40°	1.8	2.4	3.6	3.0	2.4
42.5°	1.2	1.2	1.8	1.2	1.2
45°	0.6	0.6	0.6	0.6	0.6
47.5°	0.6	0.6	0.0	0.6	0.6
50°	0.6	0.0	0.0	0.0	0.6
52.5°	0.6	0.0	0.0	0.0	0.6
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1326508  
CATALOG NUMBER: LDSQA3D09R35W2N902750DE010 3LSQPHR1MB\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)