

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1327571

Luminaire Tested: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1327571  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 90CRI ,  
3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 871.0 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1327571  
CATALOG NUMBER: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1327571  
 CATALOG NUMBER: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	95	93	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	90	93	91	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	88	92	90	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	87	91	88	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	89	87	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	84	88	86	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1116847	1116847	1116847
5°	964812	973801	977432
10°	580810	586231	615418
15°	200888	196181	211818
20°	52765	49631	49778
25°	11497	13853	15772
30°	4932	4932	5091
35°	2775	2439	2607
40°	1214	1394	1574
45°	390	560	560
50°	214	214	214
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 560 cd/sqm



TEST NUMBER: P1327571

CATALOG NUMBER: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	463.8	53.3
10°-20°	353.1	40.5
20°-30°	43.7	5.0
30°-40°	8.3	0.9
40°-50°	2.0	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.6	98.8
0°-40°	868.9	99.8
0°-60°	871.0	100.0
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	6485	6485	6485	6485	6485	
5°	5581	5577	5633	5629	5654	460
15°	1127	1086	1100	1166	1188	353
25°	60	69	73	76	83	42
35°	13	13	12	12	12	8
45°	2	2	2	2	2	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1327571  
 CATALOG NUMBER: LDSQA3D13R20W2N902750DE010 3LSQPHR1MMS\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	6484.9	6484.9	6484.9	6484.9	6484.9
1°	6454.6	6446.8	6453.0	6439.8	6467.0
2°	6351.4	6343.6	6343.6	6335.9	6339.7
3°	6158.9	6171.4	6163.6	6147.3	6168.3
4°	5896.7	5910.6	5923.0	5923.8	5926.9
5°	5580.8	5577.0	5632.8	5628.9	5653.8
6°	5220.8	5216.1	5240.2	5280.5	5330.2
7°	4825.0	4768.4	4832.8	4914.3	4981.0
8°	4312.9	4327.6	4371.9	4468.1	4521.6
9°	3878.3	3792.2	3886.1	4000.9	4059.1
10°	3321.2	3251.3	3352.2	3473.3	3519.1
12.5°	2090.5	2030.0	2062.6	2189.8	2210.0
15°	1126.7	1086.4	1100.3	1166.3	1188.0
17.5°	575.0	538.5	530.8	572.7	577.3
20°	287.9	279.4	270.8	274.7	271.6
22.5°	133.5	145.1	143.6	135.8	145.1
25°	60.5	69.1	72.9	76.0	83.0
27.5°	37.2	35.7	41.1	44.2	45.0
30°	24.8	24.1	24.8	25.6	25.6
32.5°	17.8	17.1	16.3	16.3	17.1
35°	13.2	13.2	11.6	12.4	12.4
37.5°	9.3	9.3	8.5	9.3	9.3
40°	5.4	6.2	6.2	6.2	7.0
42.5°	3.1	3.9	3.9	3.9	3.9
45°	1.6	2.3	2.3	2.3	2.3
47.5°	0.8	0.8	0.8	1.6	1.6
50°	0.8	0.8	0.8	0.8	0.8
52.5°	0.8	0.0	0.0	0.0	0.8
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)