

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1327746

Luminaire Tested: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1327746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 870.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1327746
CATALOG NUMBER: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1327746

CATALOG NUMBER: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	88	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	86	86	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	811875	811875	811875
5°	735728	742418	746049
10°	553091	557009	559597
15°	273848	265700	283405
20°	77342	78625	79468
25°	13416	25350	15924
30°	5250	5409	5548
35°	1640	1787	1787
40°	517	697	517
45°	390	195	390
50°	214	0	214
55°	240	0	240
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 390 cd/sqm



TEST NUMBER: P1327746

CATALOG NUMBER: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	374.5	43.0
10°-20°	422.3	48.5
20°-30°	65.5	7.5
30°-40°	6.6	0.8
40°-50°	0.9	0.1
50°-60°	0.2	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.3	99.1
0°-40°	868.9	99.9
0°-60°	870.0	100.0
0°-90°	870.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4714	4714	4714	4714	4714	
5°	4256	4263	4294	4312	4315	371
15°	1536	1525	1490	1557	1590	421
25°	71	105	133	102	84	59
35°	8	8	8	9	8	6
45°	2	1	1	1	2	1
55°	1	0	0	0	1	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1327746
 CATALOG NUMBER: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4714.1	4714.1	4714.1	4714.1	4714.1
1°	4694.7	4700.9	4693.9	4701.7	4700.9
2°	4645.8	4652.1	4643.5	4648.2	4648.2
3°	4545.8	4559.0	4566.7	4572.2	4576.8
4°	4413.9	4428.6	4440.3	4454.2	4454.2
5°	4255.7	4263.4	4294.4	4311.5	4315.4
6°	4067.2	4098.2	4121.5	4155.6	4134.6
7°	3878.7	3904.3	3936.8	3942.3	3957.0
8°	3664.5	3691.7	3722.0	3716.5	3704.1
9°	3403.9	3443.5	3479.2	3467.5	3483.0
10°	3162.7	3186.7	3185.1	3173.5	3199.9
11°	2882.6	2888.0	2857.8	2905.1	2876.4
12°	2550.6	2555.3	2516.5	2563.0	2592.5
13°	2232.6	2221.7	2168.2	2229.4	2266.7
14°	1866.4	1870.3	1802.0	1920.7	1911.4
15°	1535.9	1525.1	1490.2	1556.9	1589.5
17.5°	818.4	825.4	816.8	850.2	871.1
20°	422.0	433.6	429.0	442.9	433.6
22.5°	218.8	235.0	239.7	228.8	199.4
25°	70.6	104.7	133.4	101.6	83.8
27.5°	42.7	41.9	65.2	45.0	45.8
30°	26.4	25.6	27.2	27.2	27.9
32.5°	14.7	15.5	14.7	16.3	15.5
35°	7.8	8.5	8.5	9.3	8.5
37.5°	4.7	5.4	5.4	5.4	4.7
40°	2.3	3.1	3.1	2.3	2.3
42.5°	1.6	1.6	1.6	1.6	1.6
45°	1.6	0.8	0.8	0.8	1.6
47.5°	0.8	0.8	0.0	0.8	0.8
50°	0.8	0.8	0.0	0.8	0.8
52.5°	0.8	0.0	0.0	0.0	0.8
55°	0.8	0.0	0.0	0.0	0.8
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1327746
CATALOG NUMBER: LDSQA3D13R25W2N902750DE010 3LSQPHR1MMS_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)