

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P#

Luminaire Tested: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: LDSQRT3D10R129035DE010 3LSQPHUSR1MB  
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , 3LSQPHUSR1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 928.0 lumens  
Efficiency: N/A  
Efficacy: 79.3 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

### Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |     |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |     |     |     |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 116 | 114 | 113 | 111 |  | 114 | 112 | 111 | 109 |  | 108 | 107 | 106 |  | 104 | 104 | 103 |  | 101 | 101 | 100 | 98  |
| 2   | 113 | 110 | 108 | 106 |  | 111 | 108 | 106 | 104 |  | 105 | 104 | 102 |  | 103 | 101 | 100 |  | 100 | 99  | 98  | 97  |
| 3   | 110 | 107 | 104 | 102 |  | 109 | 105 | 103 | 101 |  | 103 | 101 | 99  |  | 101 | 99  | 98  |  | 99  | 98  | 96  | 95  |
| 4   | 108 | 104 | 101 | 98  |  | 107 | 103 | 100 | 98  |  | 101 | 99  | 97  |  | 99  | 97  | 96  |  | 98  | 96  | 95  | 94  |
| 5   | 106 | 102 | 98  | 96  |  | 105 | 101 | 98  | 96  |  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 97  | 95  | 93  | 92  |
| 6   | 104 | 99  | 96  | 94  |  | 103 | 99  | 96  | 94  |  | 98  | 95  | 93  |  | 96  | 94  | 93  |  | 95  | 93  | 92  | 91  |
| 7   | 102 | 98  | 94  | 92  |  | 101 | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 95  | 93  | 91  |  | 94  | 92  | 91  | 90  |
| 8   | 101 | 96  | 93  | 91  |  | 100 | 95  | 93  | 90  |  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  | 91  | 90  | 89  |
| 9   | 99  | 94  | 91  | 89  |  | 98  | 94  | 91  | 89  |  | 93  | 91  | 89  |  | 93  | 90  | 89  |  | 92  | 90  | 88  | 88  |
| 10  | 98  | 93  | 90  | 88  |  | 97  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  | 89  | 88  |  | 91  | 89  | 87  | 87  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2354559 |
| 5°  | 1521348 |
| 10° | 429259  |
| 15° | 121367  |
| 20° | 50749   |
| 25° | 22480   |
| 30° | 11475   |
| 35° | 6055    |
| 40° | 2585    |
| 45° | 706     |
| 50° | 777     |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 777 cd/sqm

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 620.0  | 66.8      |
| 10°-20°   | 224.9  | 24.2      |
| 20°-30°   | 60.2   | 6.5       |
| 30°-40°   | 18.9   | 2.0       |
| 40°-50°   | 3.6    | 0.4       |
| 50°-60°   | 0.3    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 905.2  | 97.5      |
| 0°-40°    | 924.1  | 99.6      |
| 0°-60°    | 928.0  | 100.0     |
| 0°-90°    | 928.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 928.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 13672 |      |
| 5°  | 8800  | 620  |
| 15° | 681   | 225  |
| 25° | 118   | 60   |
| 35° | 29    | 19   |
| 45° | 3     | 4    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 13671.6 |
| 1°    | 13440.9 |
| 2°    | 12791.9 |
| 3°    | 11681.5 |
| 4°    | 10302.8 |
| 5°    | 8800.0  |
| 6°    | 7233.9  |
| 7°    | 5832.1  |
| 8°    | 4488.0  |
| 9°    | 3340.0  |
| 10°   | 2454.6  |
| 11°   | 1808.5  |
| 12°   | 1361.4  |
| 13°   | 1055.7  |
| 14°   | 836.5   |
| 15°   | 680.7   |
| 17.5° | 432.6   |
| 20°   | 276.9   |
| 22.5° | 178.8   |
| 25°   | 118.3   |
| 27.5° | 80.8    |
| 30°   | 57.7    |
| 32.5° | 40.4    |
| 35°   | 28.8    |
| 37.5° | 20.2    |
| 40°   | 11.5    |
| 42.5° | 5.8     |
| 45°   | 2.9     |
| 47.5° | 2.9     |
| 50°   | 2.9     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P#  
CATALOG NUMBER: LDSQRT3D10R129035DE010 3LSQPHUSR1MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)