

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P#

Luminaire Tested: LDSQRT3D02R089727DE010 3LSQPHUSR1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: LDSQRT3D02R089727DE010 3LSQPHUSR1MW
Description: 3in Adjustable LED luminaire with, R08 optic, 2700K CCT AND, 97CRI , 3LSQPHUSR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 4.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P#
CATALOG NUMBER: LDSQRT3D02R089727DE010 3LSQPHUSR1MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D02R089727DE010 3LSQPHUSR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	116	114	113	111		114	112	111	110		108	107	106		105	104	103		101	101	100	99
2	113	111	108	106		111	109	107	105		106	104	103		103	102	101		101	100	99	97
3	111	108	105	103		109	106	104	102		104	102	100		102	100	99		100	98	97	96
4	109	105	102	100		108	104	101	99		102	100	98		100	99	97		99	97	96	95
5	107	103	100	98		106	102	99	97		101	98	97		99	97	96		98	96	95	94
6	105	101	98	96		104	100	98	96		99	97	95		98	96	95		97	95	94	93
7	104	100	97	95		103	99	96	94		98	96	94		97	95	94		96	94	93	92
8	103	98	95	93		102	98	95	93		97	95	93		96	94	93		95	94	92	92
9	101	97	94	92		101	97	94	92		96	94	92		95	93	92		95	93	92	91
10	100	96	93	91		100	96	93	91		95	93	91		94	92	91		94	92	91	90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	922080
5°	384504
10°	61872
15°	17741
20°	5975
25°	2641
30°	1452
35°	1030
40°	922
45°	585
50°	429
55°	240
60°	276
65°	326
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 585 cd/sqm

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D02R089727DE010 3LSQPHUSR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	77.1
10°-20°	33.4	16.2
20°-30°	7.3	3.5
30°-40°	3.2	1.5
40°-50°	1.9	0.9
50°-60°	0.8	0.4
60°-70°	0.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	200.4	96.8
0°-40°	203.5	98.3
0°-60°	206.3	99.7
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5354	
5°	2224	160
15°	100	33
25°	14	7
35°	5	3
45°	2	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D02R089727DE010 3LSQPHUSR1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5354.0
2.5°	4475.1
5°	2224.1
7.5°	829.2
10°	353.8
12.5°	182.6
15°	99.5
17.5°	56.3
20°	32.6
22.5°	21.2
25°	13.9
27.5°	10.6
30°	7.3
32.5°	5.7
35°	4.9
37.5°	4.1
40°	4.1
42.5°	3.3
45°	2.4
47.5°	1.6
50°	1.6
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)