

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744292

Luminaire Tested: LD4D20D010-EU4DR4020359035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P744292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR4020359035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2032.2 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744292

CATALOG NUMBER: LD4D20D010-EU4DR4020359035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P744292

CATALOG NUMBER: LD4D20D010-EU4DR4020359035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	516956
5°	514445
10°	486255
15°	413379
20°	281752
25°	117554
30°	36966
35°	17180
40°	9499
45°	4357
50°	2108
55°	1162
60°	612
65°	207
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4357 cd/sqm



TEST NUMBER: P744292

CATALOG NUMBER: LD4D20D010-EU4DR4020359035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.0	21.6
10°-20°	981.2	48.3
20°-30°	491.1	24.2
30°-40°	90.0	4.4
40°-50°	24.8	1.2
50°-60°	5.8	0.3
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1910.3	94.0
0°-40°	2000.3	98.4
0°-60°	2031.0	99.9
0°-90°	2032.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2032.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4731	
5°	4690	438
15°	3654	981
25°	975	491
35°	129	90
45°	28	25
55°	6	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744292

CATALOG NUMBER: LD4D20D010-EU4DR4020359035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4731.4
2.5°	4724.4
5°	4690.5
7.5°	4582.1
10°	4382.8
12.5°	4072.2
15°	3654.5
17.5°	3111.4
20°	2423.2
22.5°	1652.0
25°	975.1
27.5°	515.5
30°	293.0
32.5°	189.4
35°	128.8
37.5°	92.0
40°	66.6
42.5°	45.6
45°	28.2
47.5°	18.0
50°	12.4
52.5°	8.8
55°	6.1
57.5°	3.9
60°	2.8
62.5°	1.7
65°	0.8
67.5°	0.6
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)