

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750649

Luminaire Tested: LD4D60D010-EU4DR3055659024-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3055659024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5034.7 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750649

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P750649

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1239153	1239153	1239153
5°	1203579	1202173	1203640
10°	1042484	1035131	1042235
15°	680163	676510	673111
20°	338213	350903	337765
25°	170365	192121	166877
30°	68215	74323	59430
35°	31640	30303	25398
40°	13659	15168	12870
45°	9634	11961	9721
50°	3310	8705	3501
55°	1908	3603	2015
60°	1332	1577	1332
65°	869	869	869
70°	537	358	537
75°	0	237	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 11961 cd/sqm



TEST NUMBER: P750649

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1423.6	28.3
10°-20°	2292.7	45.5
20°-30°	990.7	19.7
30°-40°	225.8	4.5
40°-50°	77.5	1.5
50°-60°	18.9	0.4
60°-70°	4.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4706.9	93.5
0°-40°	4932.8	98.0
0°-60°	5029.2	99.9
0°-90°	5034.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5034.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	16189	16189	16189	16189	16189	
5°	15664	15649	15646	15679	15665	1425
15°	8583	8480	8537	8509	8494	2298
25°	2017	2094	2275	2040	1976	966
35°	339	346	324	322	272	230
45°	89	110	110	110	90	63
55°	14	15	27	16	15	14
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P750649

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	16188.9	16188.9	16188.9	16188.9	16188.9
2.5°	16081.6	16070.4	16076.8	16084.7	16087.9
5°	15664.3	15649.2	15646.0	15678.6	15665.1
7.5°	14822.6	14801.1	14768.5	14842.4	14911.6
10°	13412.6	13388.7	13318.0	13352.9	13409.4
12.5°	11330.9	11253.8	11252.2	11363.5	11348.4
15°	8583.2	8479.9	8537.1	8509.3	8494.2
17.5°	5772.0	5732.2	5808.5	5785.5	5686.1
20°	4152.1	4162.5	4307.9	4234.8	4146.6
22.5°	3029.8	3067.2	3239.7	3051.3	2982.2
25°	2017.2	2093.6	2274.8	2040.3	1975.9
27.5°	1240.7	1275.7	1459.3	1224.8	1189.8
30°	771.8	754.3	840.9	721.7	672.4
32.5°	506.3	484.0	511.9	459.4	419.7
35°	338.6	345.7	324.3	321.9	271.8
37.5°	211.4	243.2	214.6	228.9	174.9
40°	136.7	176.4	151.8	167.7	128.8
42.5°	112.1	135.9	124.8	132.7	114.5
45°	89.0	110.5	110.5	110.5	89.8
47.5°	49.3	73.9	94.6	75.5	52.5
50°	27.8	37.4	73.1	38.9	29.4
52.5°	19.1	21.5	50.1	22.3	19.9
55°	14.3	15.1	27.0	15.9	15.1
57.5°	11.1	11.9	14.3	11.9	11.1
60°	8.7	8.7	10.3	9.5	8.7
62.5°	6.4	6.4	7.2	6.4	6.4
65°	4.8	4.8	4.8	4.8	4.8
67.5°	2.4	3.2	3.2	3.2	3.2
70°	2.4	1.6	1.6	1.6	2.4
72.5°	1.6	0.8	0.8	0.8	0.8
75°	0.0	0.0	0.8	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)