

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750651

Luminaire Tested: LD4D60D010-EU4DR3055659024-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3055659024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4491.2 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750651

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P750651

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1105394	1105394	1105394
5°	1073657	1072405	1073711
10°	929955	923395	929729
15°	606744	603487	600452
20°	301704	313026	301305
25°	151979	171379	148863
30°	60853	66297	53013
35°	28220	27033	22660
40°	12190	13529	11481
45°	8595	10673	8671
50°	2953	7764	3120
55°	1708	3216	1802
60°	1194	1408	1194
65°	779	779	779
70°	470	313	470
75°	0	207	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 10673 cd/sqm



TEST NUMBER: P750651

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1269.9	28.3
10°-20°	2045.2	45.5
20°-30°	883.8	19.7
30°-40°	201.4	4.5
40°-50°	69.2	1.5
50°-60°	16.9	0.4
60°-70°	4.4	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4198.9	93.5
0°-40°	4400.3	98.0
0°-60°	4486.4	99.9
0°-90°	4491.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4491.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14441	14441	14441	14441	14441	
5°	13973	13960	13957	13986	13974	1271
15°	7657	7565	7616	7591	7577	2050
25°	1800	1868	2029	1820	1763	861
35°	302	308	289	287	242	205
45°	79	99	99	99	80	56
55°	13	14	24	14	14	12
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P750651

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14441.4	14441.4	14441.4	14441.4	14441.4
2.5°	14345.6	14335.7	14341.4	14348.5	14351.3
5°	13973.4	13959.9	13957.1	13986.2	13974.1
7.5°	13222.6	13203.4	13174.3	13240.3	13302.0
10°	11964.8	11943.5	11880.4	11911.6	11961.9
12.5°	10107.8	10039.0	10037.6	10136.9	10123.4
15°	7656.7	7564.6	7615.6	7590.8	7577.3
17.5°	5148.9	5113.5	5181.5	5161.0	5072.3
20°	3703.9	3713.1	3842.9	3777.7	3699.0
22.5°	2702.8	2736.1	2890.0	2721.9	2660.3
25°	1799.5	1867.6	2029.2	1820.1	1762.6
27.5°	1106.8	1138.0	1301.8	1092.6	1061.4
30°	688.5	672.9	750.1	643.8	599.8
32.5°	451.6	431.8	456.6	409.8	374.4
35°	302.0	308.4	289.3	287.2	242.5
37.5°	188.6	217.0	191.4	204.2	156.0
40°	122.0	157.4	135.4	149.6	114.9
42.5°	100.0	121.2	111.3	118.4	102.1
45°	79.4	98.6	98.6	98.6	80.1
47.5°	44.0	65.9	84.4	67.4	46.8
50°	24.8	33.3	65.2	34.7	26.2
52.5°	17.0	19.1	44.7	19.9	17.7
55°	12.8	13.5	24.1	14.2	13.5
57.5°	9.9	10.6	12.8	10.6	9.9
60°	7.8	7.8	9.2	8.5	7.8
62.5°	5.7	5.7	6.4	5.7	5.7
65°	4.3	4.3	4.3	4.3	4.3
67.5°	2.1	2.8	2.8	2.8	2.8
70°	2.1	1.4	1.4	1.4	2.1
72.5°	1.4	0.7	0.7	0.7	0.7
75°	0.0	0.0	0.7	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)