

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751200

Luminaire Tested: LD4D60D010-EU4DR6555659024-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4993.1 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751200

CATALOG NUMBER: LD4D60D010-EU4DR6555659024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751200

CATALOG NUMBER: LD4D60D010-EU4DR6555659024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264786
5°	264114
10°	263889
15°	255757
20°	232834
25°	202901
30°	168753
35°	133712
40°	96506
45°	60972
50°	31783
55°	16893
60°	8866
65°	4878
70°	2049
75°	2257
80°	1581
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 60972 cd/sqm



TEST NUMBER: P751200

CATALOG NUMBER: LD4D60D010-EU4DR6555659024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	428.7	8.6
10°-20°	1174.1	23.5
20°-30°	1435.1	28.7
30°-40°	1164.4	23.3
40°-50°	580.2	11.6
50°-60°	161.8	3.2
60°-70°	36.8	0.7
70°-80°	9.6	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3037.9	60.8
0°-40°	4202.3	84.2
0°-60°	4944.3	99.0
0°-90°	4993.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4993.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4534	
5°	4505	429
15°	4230	1174
25°	3149	1435
35°	1875	1164
45°	738	580
55°	166	162
65°	35	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P751200

CATALOG NUMBER: LD4D60D010-EU4DR6555659024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4533.7
2.5°	4530.3
5°	4505.0
7.5°	4490.4
10°	4449.7
12.5°	4367.1
15°	4229.9
17.5°	4015.3
20°	3746.2
22.5°	3455.7
25°	3148.6
27.5°	2820.1
30°	2502.3
32.5°	2188.5
35°	1875.4
37.5°	1563.0
40°	1265.8
42.5°	987.3
45°	738.2
47.5°	514.3
50°	349.8
52.5°	241.2
55°	165.9
57.5°	111.9
60°	75.9
62.5°	52.6
65°	35.3
67.5°	18.0
70°	12.0
72.5°	11.3
75°	10.0
77.5°	6.7
80°	4.7
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)