

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750740

Luminaire Tested: LD4D60D010-EU4DR3555659027-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5578.3 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750740

CATALOG NUMBER: LD4D60D010-EU4DR3555659027-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P750740

CATALOG NUMBER: LD4D60D010-EU4DR3555659027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1677011
5°	1637615
10°	1475918
15°	1145550
20°	649744
25°	252782
30°	94307
35°	51686
40°	33789
45°	20566
50°	13088
55°	9239
60°	6774
65°	3671
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20566 cd/sqm



TEST NUMBER: P750740

CATALOG NUMBER: LD4D60D010-EU4DR3555659027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1373.2	24.6
10°-20°	2681.1	48.1
20°-30°	1093.5	19.6
30°-40°	261.7	4.7
40°-50°	109.1	2.0
50°-60°	45.1	0.8
60°-70°	14.1	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5147.8	92.3
0°-40°	5409.5	97.0
0°-60°	5563.6	99.7
0°-90°	5578.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5578.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15349	
5°	14931	###
15°	10127	2681
25°	2097	1093
35°	388	262
45°	133	109
55°	48	45
65°	14	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750740

CATALOG NUMBER: LD4D60D010-EU4DR3555659027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	15348.7
2.5°	15256.7
5°	14931.1
7.5°	14281.5
10°	13303.0
12.5°	11925.3
15°	10127.3
17.5°	7928.4
20°	5588.1
22.5°	3563.3
25°	2096.8
27.5°	1185.2
30°	747.5
32.5°	524.8
35°	387.5
37.5°	299.7
40°	236.9
42.5°	182.5
45°	133.1
47.5°	99.6
50°	77.0
52.5°	61.1
55°	48.5
57.5°	39.3
60°	31.0
62.5°	22.6
65°	14.2
67.5°	5.0
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)